E20246

Fibre optic diffuse reflection sensor

FT-30-A-A-M8/4M

Article no longer available - archive entry

Alternative articles: E20152
When selecting an alternative article and accessories please note that technical data may differ!



Application		
Function principle		Diffuse reflection sensor
Detection zone		
Range with fibre optic amplifier type		OIF
OIF		
Range fibre optics	[mm]	36
Operating conditions		
Ambient temperature	[°C]	-40...290
Mechanical data		
Version of sensing head		angled
Sensing head thread		M8
Total length	[mm]	4000
Min. bending radius	[mm]	30
Materials		Adapter: PA
Fibre material		glass
Fibre head material		aluminium

E20246

Fibre optic diffuse reflection sensor

FT-30-A-A-M8/4M

Fibre sheath material	aluminium
Remarks	
Pack quantity	1 pcs.