E60124

Wirable socket

SDOGK120--LFKSG



Electrical data		
Operating voltage	[V]	4.5...30 DC
Operating conditions		
Ambient temperature	[°C]	-40...125
Protection		IP 67
Mechanical data		
Weight	[g]	45
Dimensions	[mm]	28 x 28 x 53
Materials		brass in plastic sheath; PA 6.6 black
Moulded-body material		brass / PA 6.6, in plastic sheath
Remarks		
Pack quantity		1 pcs.

Electrical connection

soldering: ...1 mm²

Electrical connection - socket

Connector: 1 x M23, straight; Moulded body: brass / PA 6.6, in plastic sheath



E60124

Wirable socket

SDOGK120--LFKSG

Connection