E70079

Jumper cable with valve plug

VVDAA041--S0002A03STGH030MSS

Article no longer available - archive entry



Electrical data			
Operating voltage	[V]	< 24 AC/DC	
Overvoltage protection		yes; (VDR)	
Operating conditions			
Ambient temperature	[°C]	-25...90	
Protection		IP 67	
Mechanical data			
Dimensions	[mm]	15 x 15 x 46.5	
Materials		TPU	
Moulded-body material		TPU	
Material nut		brass, nickel-plated	
Displays / operating elements			
Display		operation	1 x LED, yellow
Accessories			
Items supplied		screw	
		panel for labelling	
Remarks			
Pack quantity		1 pcs.	

E70079

Jumper cable with valve plug

VVDAA041--S0002A03STGH030MSS

Electrical connection - plug

Connector: 1 x M12, straight; coding: A; Moulded body: TPU; Locking: brass, nickel-plated



Electrical connection

Cable: 2 m, PUR / PVC; 3 x 0.5 mm²

Connection



Electrical connection - socket

Connector: 1 x valve type A DIN, angled; Moulded body: TPU; Locking: brass, nickel-plated