U71005

AS-Interface gateway ControlLogix

AS-i MASTER (A-B)



CE

Application		
Application		AS-i master for ControlLogix PLC platform
Electrical data		
Operating voltage	[V]	30 DC; (AS-i)
Current consumption	[mA]	5,1 V DC: 390 mA; 24 V DC: 150 mA; AS-i 1: 70 mA; AS-i 2: 70 mA
Number of AS-i masters		2
Interfaces		
Communication interface		RS232
RS232		
Number of R232 interfaces		1
Transmission rate		9600...115200 Baud
Connector type		RJ11
Usage type		programming
Operating conditions		
Ambient temperature	[°C]	0...55
Storage temperature	[°C]	-25...85
Protection		IP 20
AS-i classification		
AS-i version		3.0
Mechanical data		
Weight	[g]	305
Displays / operating elements		
Display		LED bar display
Remarks		
Remarks		Configuration is handled through Allen-Bradleys' RSLogix software.

U71005

AS-Interface gateway ControlLogix

AS-i MASTER (A-B)

Pack quantity	1 pcs.