




Kotak splitter

ZDO8H059MSS0000-00STAK120MSS



Aplikasi

|                    |                                          |
|--------------------|------------------------------------------|
| Fitur khusus       | Bebas dari silikon; Kontak berlapis emas |
| Bebas dari silikon | ya                                       |

Data kelistrikan

|                                 |     |                                              |
|---------------------------------|-----|----------------------------------------------|
| Tegangan pengoperasian          | [V] | 10...30 DC; ("kelas suplai 2" menurut cULus) |
| Beban arus maks. per modul/slot | [A] | 4                                            |
| Total beban arus maks.          | [A] | 12                                           |

Output

|                    |     |
|--------------------|-----|
| Desain kelistrikan | PNP |
|--------------------|-----|



## Kotak splitter

ZDO8H059MSS0000-00STAK120MSS

| Kondisi pengoperasian                                                                        |                    |                 |
|----------------------------------------------------------------------------------------------|--------------------|-----------------|
| Suhu sekitar                                                                                 | [°C]               | -25...80        |
| Perlindungan                                                                                 |                    | IP 67           |
| Pengujian/persetujuan                                                                        |                    |                 |
| Persetujuan UL                                                                               | Tipe penutup       | Type 1          |
| Data teknis                                                                                  |                    |                 |
| Berat                                                                                        | [g]                | 304.5           |
| Dimensi                                                                                      | [mm]               | 33 x 60 x 152   |
| Material                                                                                     |                    | PA              |
| Material bodi detakan                                                                        |                    | PA              |
| Jumlah port kotak splitter                                                                   |                    | 8               |
| Tipe konektor                                                                                |                    | M12             |
| Elemen display/pengoperasian                                                                 |                    |                 |
| Display                                                                                      | status peralihan   | 8 x LED, kuning |
|                                                                                              | operasi            | 1 x LED, hijau  |
| Aksesori                                                                                     |                    |                 |
| Item dikirim                                                                                 | Tutup pelindung: 2 |                 |
|                                                                                              | label: 8           |                 |
| Keterangan                                                                                   |                    |                 |
| Jumlah paket                                                                                 | 1 buah             |                 |
| Koneksi listrik - Koneksi                                                                    |                    |                 |
| Konektor: 1 x M23; Bodi cetakan: PA; Kontak: dilapisi emas; Torsi pengencangan: 0.8...1.5 Nm |                    |                 |



## Kotak splitter

ZDO8H059MSS0000-00STAK120MSS

## Koneksi



## Koneksi listrik - slot

Konektor: 8 x M12; pengkodean: A; Bodi cetakan: PA; Kontak: dilapisi emas; Torsi pengencangan: 0.8...1.5 Nm

