




AS-Interface control cabinet module

Modul aktiv, 4E 200mA/4AT PNP

Article no longer available - archive entry

Alternative article: AC2257 When selecting an alternative article and accessories please note that technical data may differ! – When selecting an alternative article and accessories please note that technical data may differ!



1 addressing socket



Electrical data

| | | |
|-------------------------|------|----------------|
| Operating voltage | [V] | 26.5...31.6 DC |
| Current consumption | [mA] | < 235 |
| Max. current load total | [A] | 4 |
| Integrated watchdog | | yes |

Inputs / outputs

| | |
|------------------------------|---|
| Number of inputs and outputs | Number of digital inputs: 4; Number of digital outputs: 4 |
|------------------------------|---|

Inputs


| | |
|---|--------------------|
| Number of digital inputs | 4; (bidirectional) |
| Input circuit of digital inputs | PNP |
| Sensor supply of the inputs | AS-i |
| Voltage supply | [V] 20...30 |
| Max. total current rating of inputs | [mA] 200 |
| Input current High | [mA] > 5 |
| Input current Low | [mA] < 1.5 |
| Min. switching level high signal | [V] 10 |
| Digital inputs protected against short circuits | yes |



AS-Interface control cabinet module

Modul aktiv, 4E 200mA/4AT PNP

| Outputs | | |
|-----------------------------------|----------------------|-------------|
| Electrical design | AS-i | |
| Number of digital outputs | 4 | |
| Circuit | PNP | |
| Voltage range DC [V] | 10...30; (to PELV) | |
| Max. current load per output [mA] | 1000 | |
| Short-circuit proof | yes | |
| Electrically separated | yes | |
| Operating conditions | | |
| Ambient temperature [°C] | -25...80 | |
| Protection | IP 20 | |
| Tests / approvals | | |
| EMC | EN 50295 | |
| AS-i classification | | |
| AS-i profile | S-7.0 | |
| AS-i I/O configuration [hex] | 7 | |
| AS-i ID code [hex] | 0 | |
| AS-i certificate | 05001 | |
| Mechanical data | | |
| Type of mounting | mounting on DIN rail | |
| Materials | PA; PVC | |
| Displays / operating elements | | |
| Display | switching status | LED, yellow |
| | operation | LED, green |
| Remarks | | |
| Pack quantity | 1 pcs. | |
| Electrical connection | | |
| Connection | | |



Article no longer available - archive entry

Alternative article: AC2257 When selecting an alternative article and accessories please note that technical data may differ! – When selecting an alternative article and accessories please note that technical data may differ!