

O5D101



Photoelectric distance sensor

O5DLCPKG/US



- 1: setting pushbuttons
2: alphanumeric display 3-digit
3: Tightening torque < 2 Nm when using a mounting screw M5

receiver in upper lens
transmitter in lower lens



Product characteristics

Type of light	red light
Laser protection class	2
Housing	rectangular

Application

Special feature	Background suppression
-----------------	------------------------

Electrical data

Operating voltage	[V]	10...30 DC; ("supply class 2" to cULus)
Current consumption	[mA]	< 75; (@ 24 V DC)
Protection class		III
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	650
Typ. lifetime	[h]	50000



Photoelectric distance sensor

O5DLCPKG/US

Inputs / outputs			
Number of inputs and outputs		Number of digital outputs: 2	
Outputs			
Total number of outputs		2	
Electrical design		PNP	
Number of digital outputs		2	
Output function		normally open / normally closed; (complementary)	
Max. current load per output	[mA]	100	
Switching frequency DC	[Hz]	11	
Short-circuit protection		yes	
Type of short-circuit protection		pulsed	
Overload protection		yes	
Detection zone			
Max. light spot diameter	[mm]	5	
Light spot dimensions refer to		2 m	
Detection range hysteresis	[%]	< 2.5	
Note on monitoring range hysteresis		black 6% remission	
Background suppression available		yes	
Background suppression	[m]	< 20	
Measuring/setting range			
Measuring range	[m]	0.03...2	
Sampling rate	[Hz]	33	
Interfaces			
Communication interface		IO-Link	
Transmission type		COM2 (38,4 kBaud)	
IO-Link revision		1.1	
SDCI standard		IEC 61131-9	
Profiles		Smart Sensor: Sensor Identification; Binary Data Channel; Process Value; Sensor Diagnosis	
SIO mode		yes	
Process data analogue		1	
Process data binary		1	
Min. process cycle time	[ms]	6.6	
Supported DeviceIDs		Type of operation	DeviceID
		default	393
Operating conditions			
Ambient temperature	[°C]	-25...60	
Note on ambient temperature		at ta < -10 °C warm-up is necessary, laser is off	
Protection		IP 65; IP 67	
Max. immunity to extraneous light	[klx]	10; (on the object)	



Photoelectric distance sensor

O5DLCPKG/US

Tests / approvals		
EMC	EN 60947-5-2	
Laser protection class		2
Notes on laser protection	Caution:	laser light
	Power:	$\leq 4,0$ mW
	Wave length:	650 nm
	pulse:	1,3 ns
	Do not stare into beam.	
	Avoid exposure to the laser light.	
	laser class:	2
		EN / IEC60825-1:2007
		EN / IEC60825-1:2014
		Complies with 21 CFR 1040 except for deviations pursuant to Laser Notice No. 50, dated June 2007.
MTTF	[years]	151
Mechanical data		
Weight	[g]	60
Housing		rectangular
Dimensions	[mm]	56 x 18.2 x 46.8
Materials		housing: PA; bezel: stainless steel; operator interface: TPU; lens: PMMA
Lens alignment		side lens
Displays / operating elements		
Display	switching status	LED, yellow switching output PIN 4
	operation	LED, green
	display	alphanumeric display, 3-digit
Display unit		inch
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Connector: 1 x M12; coding: A		
		



Photoelectric distance sensor

O5DLCPKG/US

Connection



4: OUT / IO-Link

Other data


accuracy

	accuracy			
distance	black (6 % remission)	white (90 % remission)		
0 mm	± 15 mm	± 15 mm		
500 mm	± 15 mm	± 15 mm		
1000 mm	± 15 mm	± 15 mm		
1500 mm	± 20 mm	± 20 mm		
2000 mm	± 30 mm	± 20 mm		

Extraneous light on the object < 10 klx

Diagrams and graphs

hysteresis graph



x: distance [mm]
y: Hysteresis [mm]
1 = background black 6% remission
2 = background white 90% remission