


SDG850



Compressed air meter

SDG8"/METRIS PB DN200



CE IO-Link UK
CA

Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1	
Measuring range	0.6...143.9 m/s	73...17480 m³/h
Process connection	flange DN200 according to DIN EN 10220	

Application

Application	for industrial applications
Media	compressed air
Medium temperature [°C]	-10...60
Min. bursting pressure [bar]	64
Min. bursting pressure [MPa]	6.4
Pressure rating [bar]	16
Pressure rating [MPa]	1.6

Electrical data

Operating voltage [V]	18...30 DC; (to SELV/PELV)
Current consumption [mA]	< 80
Protection class	III

SDG850



Compressed air meter

SDG8"/METRIS PB DN200

Reverse polarity protection		yes
Power-on delay time	[s]	1
Inputs / outputs		
Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1	
Inputs		
Inputs	counter reset	
Outputs		
Output signal	switching signal; analogue signal; pulse signal; IO-Link; (configurable)	
Electrical design	PNP/PNP	
Number of digital outputs	2	
Output function	normally open / normally closed; (parameterisable)	
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	150; (per output)
Number of analogue outputs	1	
Analogue current output	[mA]	4...20; (scalable)
Max. load	[Ω]	500
Pulse output	consumed quantity meter	
Short-circuit protection	yes	
Type of short-circuit protection	pulsed	
Overload protection	yes	
Measuring/setting range		
Measuring range	0.6...143.9 m/s	73...17480 m³/h
Display range	1.2...172.7 m/s	146...20976 m³/h
In steps of	0.1 m/s	1 m³/h
Pressure monitoring		
Measuring range	[bar]	-1...16
Display range	[bar]	-1...20
Resolution	[bar]	0.05
Set point SP	[bar]	-0.92...16
Reset point rP	[bar]	-1...15.92
Analogue start point	[bar]	-1...12.8
Analogue end point	[bar]	2.2...16
In steps of	[bar]	0.01
Volumetric flow quantity monitoring		
Measuring range	0...100000000 m³	0...353146667.2 scf
Display range	0...10000000 m³	0...353146667.2 scf
Set point SP	0.001...10000000 m³	0.05...353146667.2 scf
Pulse value	0.001...10000000 m³	0.05...353146667.2 scf
In steps of	0.0001 m³	0.005 scf
Pulse length	[s]	0.002...2
Temperature monitoring		
Measuring range	-10...60 °C	14...140 °F

SDG850



Compressed air meter

SDG8"/METRIS PB DN200

Display range	-24...74 °C	-11.2...165.2 °F
Resolution	0.2 °C	0.5 °F
Set point SP	-9.7...60 °C	14.6...140 °F
Reset point rP	-10...59.7 °C	14...139.4 °F
Analogue start point	-10...46 °C	14...114.8 °F
Analogue end point	4...60 °C	39.2...140 °F
In steps of	0.1 °C	0.1 °F

Accuracy / deviations

Accuracy (in the measuring range)	class 141: ± (3 % MW + 0,3 % MEW); class 344: ± (6 % MW + 0,6 % MEW) ; air quality to ISO 8573-1:2010; reference conditions: inlet pipe length >= 302 cm outlet pipe length >= 51 cm; reference temperature: 18..26 °C; standard volume flow 73...7896 m³/h; (standard volume flow DIN_ISO_2533 15 °C , 1013,25 mbar, 0 % r.H.)
-----------------------------------	---

Pressure monitoring

Repeatability [% of the final value]	± 0,2
Characteristics deviation [% of the final value]	< ± 0,5; (BFSL = Best Fit Straight Line)
Greatest TEMPCO of the span [% MEW / 10 K]	± 0,3
Greatest TEMPCO of the zero point [% MEW / 10 K]	± 0,1

Temperature monitoring

Accuracy [K]	± 0,5; (medium flow in the limit area of the flow measurement range)
--------------	--

Response times

Response time [s]	0.1; (dAP = 0)
Damping process value dAP [s]	0...5
Pressure monitoring	
Response time [s]	0.05
Temperature monitoring	
Dynamic response T05 / T09 [s]	T09 = 0,5

Software / programming

Parameter setting options	hysteresis / window; normally open / normally closed; current/pulse output; display can be rotated and switched off; Display unit; totaliser
---------------------------	--

Interfaces

Communication interface	IO-Link
Transmission type	COM2 (38,4 kBaud)
IO-Link revision	1.1
SDCI standard	IEC 61131-9 CDV
Profiles	Digital Measuring Sensor (0x800A), Identification and Diagnosis (0x4000)
SIO mode	yes
Required master port type	A
Process data analogue	8
Process data binary	2
Min. process cycle time [ms]	7.2

SDG850



Compressed air meter


SDG8"/METRIS PB DN200

Supported DeviceIDs	Type of operation	DeviceID
	default	1545
Operating conditions		
Ambient temperature	[°C]	0..60
Storage temperature	[°C]	-20..85
Max. relative air humidity	[%]	90
Protection		IP 65; IP 67
Tests / approvals		
EMC	DIN EN 60947-5-9	
Vibration resistance	DIN EN 68000-2-6	5 g (10...2000 Hz)
MTTF [years]		167
Pressure Equipment Directive	Modul A; can be used for group 2 fluids; group 1 fluids on request	
Mechanical data		
Weight [g]	37790	
Materials	PBT+PC-GF30; PPS GF40; stainless steel (304/1.4301); stainless steel (303/1.4305); stainless steel (316L/1.4404); FKM	
Materials (wetted parts)	stainless steel (304/1.4301); stainless steel (316L/1.4404); FKM; ceramics glass passivated; PPS GF40; Al2O3 (ceramics); acrylate; pipe section: steel galvanised	
Process connection	flange DN200 according to:DIN EN 10220	
Displays / operating elements		
Display	colour display 1,44", 128 x 128 pixels 2 x LED, yellow	
Remarks		
Remarks	MW = measured value MEW = Final value of the measuring range D = inside pipe diameter Measuring, display and setting ranges refer to the standard volume flow according to DIN ISO 2533. For information about installation and operation please see the operating instructions.	
Pack quantity	1 pcs.	
Electrical connection		
Connector: 1 x M12; coding: A		

Compressed air meter

SDG8"/METRIS PB DN200

Connection



- OUT1/IO-Link:
switching output flow
switching output temperature
switching output pressure
Pulse output quantity meter
signal output Preset counter
- OUT2/InD:
switching output flow
switching output temperature
switching output pressure
analogue output flow
analogue output temperature
analogue output pressure
signal output Preset counter
Pulse output quantity meter
input counter reset