


VSA004

Acceleration sensor

VIBRATION SENSOR



Product characteristics

Measuring range of vibration	[g]	-25...25
------------------------------	-----	----------

Frequency range	[Hz]	1...10000
-----------------	------	-----------

Measuring principle	capacitive
---------------------	------------

Application

Special feature	Halogen-free; Screened cable; Drag chain suitability
-----------------	--

Design	for connection to external diagnostic electronics VSE
--------	---

Application	vibration detection
-------------	---------------------

Electrical data

Operating voltage	[V]	7.2...10.8 DC
-------------------	-----	---------------

Current consumption	[mA]	< 15
---------------------	------	------

Min. insulation resistance	[MΩ]	100; (500 V DC)
----------------------------	------	-----------------

Protection class	III
------------------	-----

Reverse polarity protection	yes
-----------------------------	-----

Sensor type	microelectromechanical system (MEMS)
-------------	--------------------------------------

Outputs

Analogue current output	[mA]	0...10
-------------------------	------	--------

Max. load	[Ω]	300
-----------	-----	-----

Measuring/setting range

Measuring range of vibration	[g]	-25...25
------------------------------	-----	----------

Frequency range	[Hz]	1...10000
-----------------	------	-----------

Measuring principle	capacitive
---------------------	------------

Sensitivity	[μ A/g]	142
-------------	--------------	-----

Number of measurement axes	1
----------------------------	---

Accuracy / deviations

Linearity deviation	0,2 %
---------------------	-------

VSA004



Acceleration sensor

VIBRATION SENSOR

Operating conditions		
Ambient temperature	[°C]	-20...80
Note on ambient temperature		cULus: < 80 °C
Storage temperature	[°C]	-20...80
Max. relative air humidity	[%]	80; (40 °C: 50 % non condensing)
Protection		IP 67
Tests / approvals		
EMC		EN 61000-6-2 EN 61000-6-3
Shock resistance		DIN EN 60068-2-27
Vibration resistance		DIN EN 60068-2-6
MTTF	[years]	2660
Mechanical data		
Weight	[g]	120.5
Type of mounting		mounting screw
Materials		housing: stainless steel (316L/1.4404)
Tightening torque	[Nm]	5
Mechanische Überlastfestigkeit	[g]	500
Drag chain suitability		yes
Drag chain suitability	bending radius for fixed installation	: min. 4 x cable diameter
	bending radius for flexible use	: min. 15 x cable diameter
Accessories		
Items supplied		head cap screw: 1 x M5 x 20, Torx 15
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 3 m, PUR, Halogen-free, Ø 4 mm, shielded; Maximum cable length: 250 m; drain wire connected to the housing; 4 x 0.14 mm ²		
blue	GND	
black	test	
brown	L+	
white	Out	
Screen	drain wire	