


AC5250



AS-Interface Airbox with quick mounting technology

AirBox 5/2 bist. 2DI-Y IP67



Application	
Application	field installation
Medium temperature [°C]	-10...50
Electrical data	
Operating voltage [V]	26.5...31.6 DC
Max. current consumption from AS-i [mA]	180
Inputs / outputs	
Number of inputs and outputs	Number of digital inputs: 2; Number of pneumatic outputs: 2
Inputs	
Number of digital inputs	2
Input circuit of digital inputs	PNP
Sensor supply of the inputs	AS-i
Power supply [V]	20...30; (via flat cable)



AS-Interface Airbox with quick mounting technology

AirBox 5/2 bist. 2DI-Y IP67

Max. total current rating of inputs	[mA]	100				
Input current High	[mA]	6...10				
Input current Low	[mA]	0...2				
Switching level high	[V]	> 11				
Digital inputs protected against short circuits		yes				
Outputs						
Number of pneumatic outputs		2; (pneumatic NO/NC selectable output ; bistable)				
Actuator supply outputs		AS-i				
Operating conditions						
Ambient temperature	[°C]	-10...55				
Protection		IP 65; IP 67				
Tests / approvals						
EMC		EN 50295				
		IEC 61000-6-2				
MTTF	[years]	286				
AS-i classification						
AS-i version		2.11; 3.0				
AS-i addressing		addressing socket				
Extended addressing mode		no				
AS-i master profile		M2; M3; M4				
AS-i profile		S-3.F.F				
AS-i I/O configuration	[hex]	3				
AS-i ID code	[hex]	F.F				
Assignment of the data bits		data bit	D0	D1	D2	D3
		input	1	2	3	4
		socket	I-1/2	I-1/2 I-2	-	-
		pin	4	2 4	-	-
		pneumatic output	-	-	4	2
Mechanical data						
Weight	[g]	383				
Type of mounting		quick mounting				
Materials		PA; POM; piercing contacts: CuSn6 nickel-plated and tin-plated				
Pneumatic system		1 x 5/2-way slide valve (free from overlapping); bistable				
Operating pressure range	[bar]	3...8				
Operating pressure range	[MPa]	0.3...0.8				
Operating pressure range	[psi]	43.5...116				
Air flow at 6/5 bar	[l/min]	500				
Permissible compressed air		non-lubricated compressed air class 6-3-1; lubricated compressed air class 6-3-4				
Manual override		pressing/releasing or pressing/turning/locking				
Tube fittings		8 mm				
Exhaust		exhaust can be discharged through tube connection				




AS-Interface Airbox with quick mounting technology

AirBox 5/2 bist. 2DI-Y IP67

Displays / operating elements		
Display	operation	LED, green
	errors	LED, red
	function	LED, yellow
Electrical connection		
Module connection	Flat cables	
Accessories		
Items supplied	lower part	
Accessories (optional)	Mounting plate:, E74999	
	Module lower part:, E75000	
	Protective cap: M12, E73004	
	sealing plugs:, E75231	
	silencer:, E75232	
	Push-in L-fitting:, E75228	
	Push-in T-fitting:, E75227	
Remarks		
Remarks	If not pneumatically operated, E75231 sealing plug must be inserted.	
	Avoid ingress of dirt and dust.	
	Do not connect any of the following points to an external potential:	
	I-, I+, I1, I2	
	The connections are electrically connected with the AS-i cable.	
	Please see the notes on compressed air and EMC/ESD under "Downloads"	
Pack quantity	1 pcs.	

Electrical connection	
quick mounting technology for AS-i flat cable: ; three orientations possible	
Connection	





AS-Interface Airbox with quick mounting technology


AirBox 5/2 bist. 2DI-Y IP67

Connector: M12

	Inputs
	socket I-1/2
1	Sensor supply L+
2	data input 2
3	Sensor supply L-
4	data input 1
5	functional earth (FE)
	socket I-2
1	Sensor supply L+
2	not used
3	Sensor supply L-
4	data input 2
5	functional earth (FE)

Diagrams and graphs

Pneumatic symbol



1 x 5/2-way slide valve (free from overlapping); bistable