


## Inductive sensor

IIK3022-APKG/US-104



## Product characteristics

|                    |                    |
|--------------------|--------------------|
| Electrical design  | PNP                |
| Output function    | normally closed    |
| Sensing range [mm] | 22                 |
| Housing            | threaded type      |
| Dimensions [mm]    | M30 x 1.5 / L = 60 |

## Application

|                 |                                                                                                                     |
|-----------------|---------------------------------------------------------------------------------------------------------------------|
| Special feature | Gold-plated contacts; Increased sensing range                                                                       |
| Application     | Suitable for industrial, mobile, cooling and lubricating applications; Industrial applications / factory automation |

## Electrical data

|                             |            |
|-----------------------------|------------|
| Operating voltage [V]       | 10...30 DC |
| Current consumption [mA]    | < 10       |
| Protection class            | III        |
| Reverse polarity protection | yes        |

## Outputs

|                                                      |                 |
|------------------------------------------------------|-----------------|
| Electrical design                                    | PNP             |
| Output function                                      | normally closed |
| Max. voltage drop switching output DC [V]            | 2.5             |
| Permanent current rating of switching output DC [mA] | 100             |
| Switching frequency DC [Hz]                          | 100             |
| Short-circuit protection                             | yes             |
| Overload protection                                  | yes             |

## Detection zone

|                               |                |
|-------------------------------|----------------|
| Sensing range [mm]            | 22             |
| Real sensing range $S_r$ [mm] | $22 \pm 10 \%$ |
| Operating distance [mm]       | 0...17.82      |
| Increased sensing range       | yes            |



## Inductive sensor

IHK3022-APKG/US-104

| Accuracy / deviations         |                           |                                                                                                                     |
|-------------------------------|---------------------------|---------------------------------------------------------------------------------------------------------------------|
| Correction factor             |                           | steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3                                         |
| Hysteresis                    | [% of Sr]                 | 3...15                                                                                                              |
| Switch point drift            | [% of Sr]                 | -10...10                                                                                                            |
| Operating conditions          |                           |                                                                                                                     |
| Ambient temperature           |                           | [-°C]                                                                                                               |
| Protection                    |                           | IP 65; IP 66; IP 67; IP 68; IP 69K                                                                                  |
| Tests / approvals             |                           |                                                                                                                     |
| EMC                           | EN 61000-4-2 ESD          | 4 kV CD / 8 kV AD                                                                                                   |
|                               | EN 61000-4-3 HF radiated  | 10 V/m                                                                                                              |
|                               | EN 61000-4-4 Burst        | 2 kV                                                                                                                |
|                               | EN 61000-4-6 HF conducted | 10 V                                                                                                                |
|                               | EN 55011                  | class B                                                                                                             |
| Vibration resistance          | EN 60068-2-6 Fc           | 20 g (10...3000 Hz) / 50 sweep cycles, 1 octave per minute, in 3 axes                                               |
| Shock resistance              | EN 60068-2-27 Ea          | 100 g 11 ms half-sine; 3 shocks each in every direction of the 3 coordinate axes                                    |
| Continuous shock resistance   | EN 60068-2-27             | 40 g 6 ms; 4000 shocks each in every direction of the 3 coordinate axes                                             |
| Fast temperature change       | EN 60068-2-14 Na          | TA = -40 °C; TB = 85 °C; t1 = 30 min; t2 = < 10 s; 50 cycles                                                        |
| Salt spray test               | EN 60068-2-52 Kb          | severity level 5 (4 test cycles)                                                                                    |
| MTTF                          | [years]                   | 1134                                                                                                                |
| Embedded software included    |                           | no                                                                                                                  |
| UL approval                   | Ta                        | -25...70 °C                                                                                                         |
|                               | Enclosure type            | Type 1                                                                                                              |
|                               | power supply              | Limited Voltage/Current                                                                                             |
|                               | UL Approval no.           | A001                                                                                                                |
|                               | File number UL            | E174191                                                                                                             |
| Mechanical data               |                           |                                                                                                                     |
| Weight                        | [g]                       | 107.8                                                                                                               |
| Housing                       |                           | threaded type                                                                                                       |
| Mounting                      |                           | non-flush mountable                                                                                                 |
| Dimensions                    | [mm]                      | M30 x 1.5 / L = 60                                                                                                  |
| Thread designation            |                           | M30 x 1.5                                                                                                           |
| Materials                     |                           | housing: brass white bronze coated; sensing face: PBT orange; LED window: PEI; lock nuts: brass white bronze coated |
| Displays / operating elements |                           |                                                                                                                     |
| Display                       | switching status          | 4 x LED, yellow                                                                                                     |
| Accessories                   |                           |                                                                                                                     |
| Items supplied                |                           | lock nuts: 2                                                                                                        |
| Remarks                       |                           |                                                                                                                     |
| Pack quantity                 |                           | 1 pcs.                                                                                                              |

# IIS236



## Inductive sensor

IIK3022-APKG/US-104

### Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: gold-plated



### Connection

