


LMT202



Sensor for point level detection

LMBCE-A34E-QSKG-2/US



1 Tightening torque 35 Nm

ACS CE cULus EC 1935/2004 FDA IO-Link KTW/W270 UKCA

Product characteristics		
Number of inputs and outputs		Number of digital outputs: 2
Factory setting		hydrous media
Process connection		G 3/4 external thread
Application		
Special feature		Gold-plated contacts
Installation		suited for installation in existing tuning fork adapters
Media		Liquids; viscous media; powder
Recommended media		water; hydrous media; oils; oil-based media; powder
Cannot be used for		See the operating instructions, chapter "Function and features".
Probe length	[mm]	28
Tank pressure	[bar]	-1...40
Oil		
Medium temperature	[°C]	-20...100
Medium temperature short time	[°C]	-20...150; (1 h)
Water		
Medium temperature	[°C]	-20...100
Medium temperature short time	[°C]	-20...150; (1 h)
Electrical data		
Operating voltage	[V]	18...30 DC
Current consumption	[mA]	< 50
Protection class		III
Reverse polarity protection		yes
Measuring principle		capacitive

LMT202



Sensor for point level detection

LMBCE-A34E-QSKG-2/US

Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 2
Outputs		
Total number of outputs		2
Output signal		switching signal; IO-Link
Electrical design		PNP/NPN
Number of digital outputs		2
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Measuring/setting range		
Factory setting		hydrous media
Response times		
Response time		[s] < 0.5
Interfaces		
Communication interface		IO-Link
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.1
SDCI standard		IEC 61131-9
Profiles		Smart Sensor: Process Data Variable; Device Identification
SIO mode		yes
Required master port type		A
Process data analogue		1
Process data binary		2
Min. process cycle time		[ms] 2.3
Supported DeviceIDs		Type of operation
		DeviceID
		default 370
Operating conditions		
Ambient temperature		[°C] -20...85
Note on ambient temperature		Medium temperature: < 100 °C
		-20...60 °C
		Medium temperature: < 150 °C
Storage temperature		[°C] -40...85
Protection		IP 68; IP 69K
Tests / approvals		
EMC		DIN EN 61000-6-2
		DIN EN 61000-6-4
		DIN EN 61000-6-3
Shock resistance		DIN EN 60068-2-27 50 g (11 ms)

LMT202



Sensor for point level detection

LMBCE-A34E-QSKG-2/US

Vibration resistance	DIN EN 60068-2-6	20 g (10...2000 Hz)
MTTF [years]		223
UL approval	UL Approval no.	H001

Mechanical data		
Weight [g]		145.7
Dimensions [mm]		Ø 30 / L = 112
Materials		stainless steel (316L/1.4404); PEEK; PEI; FKM
Materials (wetted parts)		PEEK; surface characteristics: Ra < 0,8 / Rz 4
Process connection		G 3/4 external thread

Displays / operating elements		
Display	switching status	LED, yellow
	operating status	LED, green


Remarks	
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



OUT1: switching output IO-Link Teach
OUT2: switching output
colours to DIN EN 60947-5-2