


OGE301



Through-beam sensor receiver

OGE-HPKG/US100



Product characteristics

Type of light	red light
Housing	threaded type

Application

Function principle	Through-beam sensor
--------------------	---------------------

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	10
Protection class	II
Reverse polarity protection	yes
Type of light	red light
Wave length [nm]	624

Outputs

Electrical design	PNP
Output function	light-on mode
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	150; (200 (...60 °C))
Switching frequency DC [Hz]	1000
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Transmitter / receiver	receiver
Range [m]	< 20
Range adjustable	no

Operating conditions

Ambient temperature [°C]	-25...80
--------------------------	----------

OGE301



Through-beam sensor receiver

OGE-HPKG/US100

Protection	IP 65; IP 67; IP 68; IP 69K
------------	-----------------------------

Tests / approvals

EMC	EN 60947-5-2
-----	--------------

MTTF [years]	1067
--------------	------

Mechanical data

Weight [g]	60.1
------------	------

Housing	threaded type
---------	---------------

Dimensions [mm]	M18 x 1 / L = 60
-----------------	------------------

Thread designation	M18 x 1
--------------------	---------

Materials	housing: stainless steel (316L/1.4404); Sealing: EPDM
-----------	---

Lens material	PMMA
---------------	------

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories

Items supplied	lock nuts: 2
----------------	--------------

Remarks

Remarks	operating voltage "supply class 2" according to cULus
---------	---


Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A



Connection





Through-beam sensor receiver

OGE-HPKG/US100

Diagrams and graphs

excess gain graph

