


AS-Interface power supply

PSU-1AC/ASI-4A



Electrical data

Frequency AC	[Hz]	47...64
Operating voltage tolerance	[%]	10
Operating voltage	[V]	automatic range selection
Nominal voltage AC	[V]	110 / 230
Input voltage range AC	[V]	100...120 / 200...240
Protection class		I
Overvoltage protection		yes; (< 36 V)
Max. power-on delay time	[ms]	900
Output voltage AS-i	[V]	30,5
Output power (permanent)	[W]	122
Output power (peak)	[W]	134
Note on output power (peak)	[W]	briefly to load bus capacities after power on
Power factor (nominal voltage 120 V AC / 60 Hz)		0.56
Power factor (nominal voltage 230 V AC / 50 Hz)		0.47
Power reserve	[%]	10
Number of output circuits		1
Output current AS-i	[A]	4
Max. residual ripple	[mV]	50

AC1254



AS-Interface power supply

PSU-1AC/ASi-4A

Switch-on peak current (nominal voltage 120 V AC / 60 Hz)	[A]	3
Switch-on peak current (nominal voltage 230 V AC / 50 Hz)	[A]	3
Inrush current limitation		yes
Efficiency (nominal voltage 120 V AC / 60 Hz)	[%]	88
Efficiency (nominal voltage 230 V AC / 50 Hz)	[%]	89.3
External input protection		≤ B-10 A / ≤ C-6 A
Derating	[W/K]	3 (60...70 °C)
Mains buffering time (nominal voltage 120 V AC / 60 Hz)	[ms]	70
Mains buffering time (nominal voltage 230 V AC / 50 Hz)	[ms]	70
Input current (nominal voltage 120 V AC / 60 Hz)	[A]	2.05
Input current (nominal voltage 230 V AC / 50 Hz)	[A]	1.23
Power loss (nominal voltage 120 V AC / 60 Hz)	[W]	16.6
Power loss (nominal voltage 230 V AC / 50 Hz)	[W]	14.6
Integrated data decoupling		yes
Back feeding protection	[V]	35
Outputs		
Short-circuit proof		yes
Overload protection		yes
Overload performance		output current constant
Parallel connection of outputs possible		no
Series connection of outputs possible		no
Operating conditions		
Ambient temperature	[°C]	-25...70
Note on ambient temperature		observe the free space for convection (see operating instructions)
Storage temperature	[°C]	-40...85
Max. relative air humidity	[%]	95; (IEC 60068-2-30)
Protection		IP 20
Pollution degree		2; (IEC 62103: conductive soiling not permitted)
Tests / approvals		
EMC		EN 61000-6-1
		EN 61000-6-2
		EN 61000-6-4
Vibration resistance		IEC 60068-2-6
Shock resistance		IEC 60068-2-27
MTTF	[years]	90

AC1254



AS-Interface power supply

PSU-1AC/ASI-4A

AS-i classification

AS-i certificate	98601
------------------	-------

Mechanical data

Weight [g]	625.5
Type of mounting	rail; (TH35 (EN 60715))
Dimensions [mm]	124 x 40 x 120
Materials	steel sheet

Displays / operating elements

Display	AS-i voltage	LED, green
---------	--------------	------------


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

screw terminals:

Connection




1: primary

2: secondary

Diagrams and graphs


block diagram




AS-Interface power supply

PSU-1AC/ASI-4A


output characteristics

Output Voltage

characteristic curve for degree of efficiency / power loss

Efficiency

characteristic line for derating

Allowed Output Current

characteristic line for mains buffering time

Hold-up Time