




Switched-mode power supply 24 V DC

POWER SUPPLY/24VDC/30A

phase-out article

Alternative articles: E84036
When selecting an alternative article and accessories please note that technical data may differ!



Electrical data		
Nominal voltage AC	[V]	400...500
Nominal frequency AC	[Hz]	47...63
Input voltage DC	[V]	450...820
Input voltage range AC	[V]	340...576
Output voltage DC	[V]	24...28
Protection class		I; (IEC 61140)
Max. power-on delay time	[ms]	80
Power-on delay time	[s]	< 80
Output voltage	[V]	adjustable
Output voltage tolerance	[%]	2
Max. output current at min. output voltage	[A]	30
Number of output circuits		1
Max. residual ripple	[%]	0.1
Derating	[W/K]	18 (60...70 °C)
Outputs		
Short-circuit protection		yes
Overload protection		yes


DN2036



Switched-mode power supply 24 V DC

POWER SUPPLY/24VDC/30A

Operating conditions		
Ambient temperature	[°C]	-10...60
Protection		IP 20
Tests / approvals		
EMC	EN 50081-1	
	EN 61000-6-2	
MTTF	[years]	49
Mechanical data		
Weight	[g]	2507.5
Type of mounting		rail; (TH35 (EN 60715))
Materials		aluminium
Displays / operating elements		
Display	Output voltage	1 x LED, green
	fault	1 x LED, red
Remarks		
Pack quantity		1 pcs.
Electrical connection		
terminals: 1.5...6 mm²		
Connection		



- 1
- primary
- 2
- secondary