


AC2916



AS-Interface ProcessLine module

ProcessLine 4AI C IP69K



1 LED



Application

Application	hygienic and wet areas in the food industry
-------------	---

Electrical data

Operating voltage [V]	26.5...31.6 DC
Max. current consumption [mA] from AS-i	450
Reverse polarity protection	yes

Inputs / outputs

Number of inputs and outputs	Number of analogue inputs: 4
------------------------------	------------------------------

Inputs

Sensor supply of the inputs	AS-i
Number of analogue inputs	4; (connection of 2- and 3-wire sensors)
Analogue input (current) [mA]	4...20
Analogue input (voltage) [V]	18...30
Max. voltage drop across load for nominal voltage	10
Resolution of analogue input	1 bit = 1 µA
Precision analogue input [%]	0,5

Operating conditions

Ambient temperature [°C]	-5...70
Storage temperature [°C]	-25...85
Max. relative air humidity [%]	90; (linearly decreasing to 50 % (40 °C) non condensing)
Max. height above sea level [m]	2000
Protection	IP 68; IP 69K
Pollution degree	2

Tests / approvals

EMC	EN 62026-2
	EN 61000-6-2

AC2916



AS-Interface ProcessLine module

ProcessLine 4AI C IP69K


MTTF	[years]	98
AS-i classification		
AS-i version		2.11; 3.0
Extended addressing mode		no
AS-i master profile		M3; M4
AS-i profile		S-7.3.E
AS-i I/O configuration	[hex]	7
AS-i ID code	[hex]	3.E
AS-i certificate		101108
Mechanical data		
Weight	[g]	607
Dimensions	[mm]	Ø 137.3 / L = 80
Materials		threaded bush: stainless steel (316L/1.4404); LED-Fenster: PC; O-ring: EPDM; Protective cap: PP
Displays / operating elements		
Display	analogue signal	LED, yellow channels AI1...AI4
	operation	LED, green AS-i
	errors	LED, red
Electrical connection		
Module connection		M12
Accessories		
Accessories (optional)		Protective cap: M12, E70297
		Flat cable insulation displacement connector: E70455
		Torque wrench: E70390
Remarks		
Remarks		When the sensors and actuators are supplied from AS-i the load must not exceed a maximum of 380 mA.
		The load for an individual sensor connection must not exceed 200 mA.
		There is an electrical connection between the sensor and AS-i.
		MEW = % of the final value of the measuring range
Pack quantity		1 pcs.
Electrical connection - AS-i		
Connector: 1 x M12; coding: A; Tightening torque: 1.2...1.4 Nm		
1:	AS-i +	
2:	n.c.	
3:	AS-i -	
4:	n.c.	
5:	functional earth (FE)	

AS-Interface ProcessLine module

ProcessLine 4AI C IP69K

Electrical connection - Process connection

Connector: 4 x M12; coding: A; Tightening torque: 1.2...1.4 Nm



Inputs

1	Sensor supply + 24 V
2	AI+
3	Sensor supply 0 V / AI-
4	n.c.
5	functional earth (FE)