




RFID tag

ID-TAG/D50X3.3/04

Article no longer available - archive entry



Application

Application	RFID coding in production control	
Operating temperature (active) [°C]	-40...85	
Peak temperature (passive) [°C]	140; (duration of test: 1 x 100 h)	

Electrical data

Operating frequency [MHz]	865...870	
Memory size [bit]	240	
Max. read cycles	unlimited	
Max. write cycles	100000	

Operating conditions

Ambient temperature [°C]	-20...85	
Storage temperature [°C]	-40...90	
Protection	IP 68	

Tests / approvals

Shock resistance	DIN IEC 68-2-29	40 g 18 ms
Vibration resistance	DIN IEC 68-2-6	10 g 10...2000 Hz

Mechanical data

Weight [g]	11.6	
Dimensions [mm]	Ø 50 / L = 3.3	
Materials	PA 6	

Remarks

Remarks	Storage temperature 1 x 1000 h (90 °C), 1 x 100 h (140 °C)	
	ISO-Standard EPC-Global Class 1 Gen 2	
Pack quantity	1 pcs.	