



- 1 COMBICON connector
- 2 Ethernet interface
- 3 DIN rail adapter



### Product characteristics

Frequency range	[Hz]	0.1...12000
Communication interface		Ethernet

### Application

Design	parameter setting via PC software VES004
Application	continuous vibration monitoring

### Electrical data

Operating voltage tolerance	[%]	20
Operating voltage	[V]	24 DC; (when using the IEPE input: 24 V + 20%; IEPE = Integrated Electronics Piezo Electric)
Current consumption	[mA]	200; ((24 V DC))
Protection class		III

### Inputs / outputs

Total number of inputs and outputs	8; (configurable)
Number of inputs and outputs	Number of analogue inputs: 2; number of dynamic inputs: 4; Number of digital outputs: 2; Number of analogue outputs: 1

### Inputs

Total number of inputs	6
Number of analogue inputs	2

# VSE002

## Diagnostic electronics for vibration sensors

DIAGNOSTIC ELECTRONICS



Analogue input (current)	[mA]	4...20
Resolution of analogue input		12
Number of dynamic inputs		4
Dynamic input - signal		0...10 mA / IEPE / 4...20 mA
Dynamic input - resolution	[bit]	16
Dynamic input - frequency range	[Hz]	0,1...12000
Dynamic input - sampling rate	[kSamples]	100
<b>Outputs</b>		
Total number of outputs		2
Output signal		switching signal; analogue signal
Electrical design		PNP
Number of digital outputs		2; (configurable)
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	100
Number of analogue outputs		1; (configurable)
Analogue current output	[mA]	4...20
Max. load	[Ω]	500
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
<b>Measuring/setting range</b>		
Frequency range	[Hz]	0.1...12000
<b>Interfaces</b>		
Communication interface		Ethernet
Transmission rate		10 MBaud; 100 MBaud
Protocol		TCP/IP
<b>Operating conditions</b>		
Ambient temperature	[°C]	0...70
Storage temperature	[°C]	0...70
Protection		IP 20
<b>Tests / approvals</b>		
EMC		EN IEC 61000-6-2 EN IEC 61000-6-4
MTTF	[years]	101
UL approval		Ta 70 °C Enclosure type Type 1 power supply Limited Voltage/Current (Marking Class 2)
<b>Mechanical data</b>		
Weight	[g]	323.1

## Diagnostic electronics for vibration sensors

DIAGNOSTIC ELECTRONICS

Housing	plastic housing
Type of mounting	rail; (TH35/EN60715)
Dimensions [mm]	100 x 25.4 x 103.4
Materials	PA
<b>Data memories</b>	
History memory	yes
Data memory buffered	yes
Data memory type	ring memory; FIFO
Real-time clock	yes
Memory location	internal
Memory interval	min. 1 min
Memory size	881664 data records
<b>Accessories</b>	
Accessories (optional)	cross-over Ethernet patch cable for the direct connection to the PC
<b>Remarks</b>	
Pack quantity	1 pcs.
<b>Electrical connection</b>	
COMBICON: ; Maximum cable length: 250 m	
<b>Connection</b>	