


SU6621



Ultrasonic flow meter

SUN12XXBFRKG/US



ACS **KTW/W270 Reg31**

Product characteristics				
Measuring range	0.5...65 l/min	0.03...3.9 m³/h	8...1030 gph	0.13...17.17 gpm
Process connection	1/2" NPT DN15 external thread			
Application				
Special feature	Gold-plated contacts			
Media	ultra-pure water; water; hydrous media			
Note on media	hydrous media: for media with >10 % additives, the repeatability is the only available value			
Medium temperature	-20...100 °C		-4...212 °F	
Min. bursting pressure	150 bar		15 MPa	
Pressure rating	100 bar		10 MPa	
Vacuum resistance	[mbar]	-1000		
Electrical data				
Operating voltage	[V]	18...32 DC; (to SELV/PELV)		
Current consumption	[mA]	< 75		
Protection class		III		
Reverse polarity protection		yes		
Power-on delay time	[s]	5		
Measuring principle		ultrasonic		
Inputs				
Inputs		counter reset		



Ultrasonic flow meter

SUN12XXBFRKG/US

Outputs				
Total number of outputs	2			
Output signal	switching signal; pulse signal; analogue signal; IO-Link; frequency signal; diagnostic signal; totaliser switching signal			
Electrical design	PNP/NPN			
Output function	normally open / normally closed; (parameterisable)			
Max. voltage drop switching output DC [V]	2			
Permanent current rating of switching output DC [mA]	100			
Switching frequency DC [Hz]	0...10000			
Analogue current output [mA]	4...20			
Max. load [Ω]	500			
Pulse output	flow rate meter			
Short-circuit protection	yes			
Type of short-circuit protection	pulsed			
Overload protection	yes			
Measuring/setting range				
Measuring range	0.5...65 l/min	0.03...3.9 m³/h	8...1030 gph	0.13...17.17 gpm
Display range	-78...78 l/min	-4.68...4.68 m³/h	-1236...1236 gph	-20.61...20.61 gpm
Resolution	0.1 l/min	0.002 m³/h	1 gph	0.01 gpm
Set point SP	0.9...65 l/min	0.052...3.9 m³/h	14...1030 gph	0.23...17.17 gpm
Reset point rP	0.5...64.7 l/min	0.032...3.88 m³/h	8...1025 gph	0.14...17.08 gpm
Analogue start point ASP	-65...52 l/min	-3.9...3.12 m³/h	-1030...824 gph	-17.17...13.74 gpm
Analogue end point AEP	-52...65 l/min	-3.12...3.9 m³/h	-824...1030 gph	-13.74...17.17 gpm
Low flow cut-off LFC	0.5...3.2 l/min	0.03...0.195 m³/h	8...52 gph	0.13...0.86 gpm
Frequency end point, FEP	13...65 l/min	0.782...3.9 m³/h	207...1030 gph	3.44...17.17 gpm
Frequency at the end point FRP [Hz]	1...10000			
Volumetric flow quantity monitoring				
Pulse length [s]	0.002...2			
Pulse value	0.02...99990000 l; 0.005...26414563.515 gal			
Temperature monitoring				
Measuring range	-20...100 °C		-4...212 °F	
Display range	-44...124 °C		-47.2...255.2 °F	
Resolution	0.1 °C		0.1 °F	
Set point SP	-19.6...100 °C		-3.2...212 °F	
Reset point rP	-20...99.6 °C		-4...211.2 °F	
Analogue start point	-20...76 °C		-4...168.8 °F	
Analogue end point	4...100 °C		39.2...212 °F	
Frequency start point, FSP	-20...76 °C		4...168.8 °F	
Frequency end point, FEP	4...100 °C		4...168.8 °F	
Frequency at the end point FRP [Hz]	1...10000			



Ultrasonic flow meter

SUN12XXBFRKG/US

Accuracy / deviations		
Flow monitoring		
Accuracy (in the measuring range)		$\pm (2,0 \% \text{ MW} + 0,5 \% \text{ MEW})$
Repeatability		$\pm 0,2 \% \text{ MEW}$
Temperature monitoring		
Accuracy [K]		$\pm 2,5 (Q > 5 \% \text{ MEW})$
Temperature coefficient [% of the span / 10 K]		0,2
Response times		
Flow monitoring		
Response time [s]		$< 0,25; (dAP = 0, T09)$
Damping process value dAP [s]		0...5
Temperature monitoring		
Dynamic response T05 / T09 [s]		5,7 / 86
Software / programming		
Diagnostic functions		direction of flow detection; signal quality
Interfaces		
Communication interface		IO-Link
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.1.3
SDCI standard		IEC 61131-9: 2013-07
Profiles		Identification and Diagnosis (0x4000)
Required master port type		A
Process data analogue		3
Process data binary		2
Min. process cycle time [ms]		9.6
IO-Link process data (cyclical)	function	bit length
	totaliser	32
	Flow monitoring	32
	Temperature monitoring	32
	status	4
	Output 1	1
	Output 2	1
Supported DeviceIDs	Type of operation	DeviceID
	default	1462
Operating conditions		
Ambient temperature [°C]		-20...60
Storage temperature [°C]		-25...80
Protection		IP 67
Tests / approvals		
EMC	DIN 61326-1:2021	
Shock resistance	DIN IEC 68-2-27	20 g (11ms)
Vibration resistance	DIN IEC 68-2-6	5 g (10...2000Hz)

SU6621



Ultrasonic flow meter

SUN12XXBFRKG/US

MTTF	[years]	160
UL approval	UL Approval no.	I034
Pressure Equipment Directive	can be used for group 2 fluids; group 1 fluids on request	

Mechanical data		
Weight	[g]	524.7
Type of mounting	inlet pipe length 5xDN; outlet pipe length 1xDN	
Materials	housing: stainless steel (316L/1.4404); Display: PFA; Sealing Display: FKM; connector: POKAN	
Materials (wetted parts)	Pipe section: stainless steel (316L/1.4404)	
Process connection	1/2" NPT DN15 external thread	
Surface characteristics Ra/Rz of the wetted parts	49.21 µin	

Displays / operating elements		
Display		colour display 1,44", 128 x 128 pixels
	Switching function	2 x LED, yellow
	diagnosis	1 x LED, three-colour

Accessories		
Items supplied	package insert	

Remarks		
Remarks	MW = measured value	
	MEW = Final value of the measuring range	
	pulse and totaliser signal are only available for one of the two outputs	
	the accuracy indications are adhered to over the entire application area	
Pack quantity	1 pcs.	

Electrical connection		
-----------------------	--	--

Connector: 1 x M12; coding: A; Contacts: gold-plated



SU6621



Ultrasonic flow meter

SUN12XXBFRKG/US

Connection




- OUT1/IO-Link:
switching output volumetric flow quantity monitoring
switching output Temperature monitoring
Pulse output quantity meter
frequency output volumetric flow quantity monitoring
frequency output Temperature monitoring
Diagnostic output direction of flow detection / signal quality
signal output Preset counter
- OUT2/InD:
switching output volumetric flow quantity monitoring
switching output Temperature monitoring
Pulse output quantity meter
analogue output flow
analogue output temperature
Diagnostic output direction of flow detection / signal quality
signal output Preset counter
input counter reset

colours to DIN EN 60947-5-2


Core colours	BK= black
	BN= brown
	BU= blue
	WH= white

Diagrams and graphs

Note on pressure loss



derating ambient temperature



- 1 Ambient temperature
- 2 Medium temperature