


TSM601



Temperature cable sensor with bolt-on sensor

TSM040K2PCXX/US/



Product characteristics

Measuring range	-25...160 °C	-13...320 °F
Process connection	bolt-on sensor DN40 (Ø 38...45 mm)	

Application

Special feature	Gold-plated contacts
Measuring element	1 x Pt 1000; (to DIN EN 60751, class A)
Installation	surface mount RTD for solid bodies; camp-on solution

Electrical data

Protection class	III
------------------	-----

Measuring/setting range

Measuring range	-25...160 °C	-13...320 °F
-----------------	--------------	--------------

Accuracy / deviations

Accuracy	[K]	$0,25 \pm (0,15 \text{ K} + 0,002 \text{ x T })$; (ambient temperature influence on the accuracy: $0,02 \text{ x (Ta - T)}$)
----------	-----	--

Response times

Dynamic response T05 / T09	[s]	7,5 / 25; (reference values for moving water : (> 0,4 m/s))
----------------------------	-----	---

Operating conditions

Protection	IP 69K
------------	--------

Mechanical data

Weight	[g]	140.8
Housing		Surface temperature probe
Dimensions	[mm]	87 x 84 x 45
Materials		Mounting clamp: stainless steel (316L/1.4404); housing: PPSU; Gasket: FKM
Process connection		bolt-on sensor DN40 (Ø 38...45 mm)

TSM601



Temperature cable sensor with bolt-on sensor

TSM040K2PCXX/US/

Remarks	
Remarks	Ta = Ambient temperature
	T = Process temperature
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

