


E18515



Female cordset

ADOGH040ZDS0050H04



Application		
System		gold-plated contacts
Design		Power cable, T-coded
Electrical data		
Operating voltage	[V]	< 60 AC
Max. current load total	[A]	12
Operating conditions		
Ambient temperature	[°C]	-25...85
Protection		IP 67
Mechanical data		
Weight	[g]	5134.661
Dimensions	[mm]	15.4 x 15.4 x 52.8
Material		TPU (urethane)
Molded-body material		TPU (urethane)
Material nut		diecast zinc, nickel-plated
Remarks		
Pack quantity		1 pcs.

E18515



Female cordset


ADOGH040ZDS0050H04

Electrical connection


Cable: 50 m, PUR, black, Ø 8 mm; 4 x 1.5 mm²

Electrical connection - Socket

Connector: 1 x M12, straight; coding: T; Moulded body: TPU (urethane); Locking: diecast zinc, nickel-plated; Contacts: gold-plated



Connection



BK = Core colors :
BN = black
BU = brown
WH = blue
BK = white