


DI6001



Compact evaluation unit for speed monitoring

DGA4012-WPKG/US



- 1 LED 3 x
- 2 setting pushbutton



Product characteristics		
Electrical design		PNP
Output function		normally open / closed; (configurable)
Sensing range	[mm]	12
Housing		Threaded type
Dimensions	[mm]	M18 x 1 / L = 68
Application		
System		gold-plated contacts
Application		evaluation of rotating and linear movements with regard to underspeed; blocking
Electrical data		
Nominal voltage DC	[V]	10...36
Current consumption	[mA]	< 15
Protection class		II
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		normally open / closed; (configurable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250; (Pulse output: 15)
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes
Monitoring range		
Sensing range	[mm]	12
Sensing range adjustable		no

DI6001



Compact evaluation unit for speed monitoring

DGA4012-WPKG/US

Measuring/setting range		
Setting range	[Imp/min]	3...6000
Measuring principle		inductive
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.8 / brass: 0.5 / aluminum: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	10
Reaction times		
Start-up delay	[s]	0...15
Max. damping frequency	[Imp/min]	18000
Software / programming		
Adjustment of the switch point		Teach function
Operating conditions		
Ambient temperature	[°C]	-20...80
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
MTTF	[years]	1031
UL approval	voltage supply	Class 2
Mechanical data		
Weight	[g]	67.5
Housing		Threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M18 x 1 / L = 68
Thread designation		M18 x 1
Material		stainless steel (1.4571/316Ti); PBT
Tightening torque	[Nm]	35
Displays / operating elements		
Display	Switching status	1 x LED, yellow
	Power	1 x LED, green

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated




DI6001



Compact evaluation unit for speed monitoring

DGA4012-WPKG/US

Connection



- 2: Pulse output pulse sequence corresponds to damping frequency
4: Switching output adjustable