
# SF6200

## Flow sensor for connection to an evaluation unit

SFG10ABB /US-100







Product characteristics			
Probe length L	[mm]	15156	
Process connection		Ø 10 mm	
Application		<del>2</del>	
System		gold-plated contacts	
Application	high temperature		
Installation		Sensor suitable for clamp fitting	
Media		Liquids; Gases	
Medium temperature	[°C]	-2580	
Pressure rating	[bar]	30	
Liquids			
Application		high temperature	
Installation	Sensor suitable for clamp fitting		
Medium temperature	[°C]	-2580	
Gases			
Medium temperature	[°C]	-2580	
Electrical data			
Connection to control monitor		VS3000	
Measuring/setting range	е		
Probe length L	[mm]	15156	
Liquids			
Setting range	[cm/s]	3300	
Greatest sensitivity	[cm/s]	360	
Gases			
Setting range	[cm/s]	2003000	
Greatest sensitivity	[cm/s]	200800	
Accuracy / deviations			
Max. temperature gradient of[K/min] medium		30	
Reaction times			
Response time	[s]	110	

# SF6200

## Flow sensor for connection to an evaluation unit



SFG10ABB /US-100

Liquids				
Response time	[s]	1	10	
Gases				
Response time	[s]	110		
Operating conditions				
Protection		IP 67		
Tests / approvals				
Shock resistance		DIN IEC 68-2-27	40 g (11 ms)	
Vibration resistance		DIN IEC 68-2-6	10 g (552000 Hz)	
MTTF	[years]	8583		
Mechanical data				
Weight	[g]	89		
Dimensions	[mm]	Ø 10		
Material		stainless steel (1.4404 / 316L) several parts, welded		
Materials (wetted parts)		stainless steel (1.4404 / 316L) several parts, welded		
Process connection		Ø 10 mm		
Accessories				
Accessories (optional)		Clamp adapte	er: R 1/2, E40160	
		Clamp adapter:	1/2" NPT, E40174	
Remarks				
Pack quantity		1 pcs.		
Electrical connection				

Connector: 1 x M12; coding: A; Contacts: gold-plated; Maximum cable length: 100 m




# SF6200

## Flow sensor for connection to an evaluation unit





### Connection



Core colors:

BN =	brown
BU =	blue
BK =	black
WH =	white
GY =	grey