
SN0150

Control monitor for flow sensors



VS3000/85...265VAC

Short-circuit proof



Application Application Flow monitoring; Temperature monitoring; Wire break monitoring Electrical data Frequency AC [Hz] 47...63 Operating voltage tolerance [%] -5...10 Operating voltage [V] 90...240 AC Max. power consumption [VA] 4 Protection class Ш Reverse polarity protection no Power-on delay time [S] 10...80; (adjustable (fixed-value resistors terminals 22-23)) Number of channels 1 Outputs Performance in case of a In case of undervoltage all relays are de-energized, the fault LED "LOW VOLTAGE/WIRE BREAK-RELAY" lights Electrical design Relay Contact rating 4 A (250 V AC / 30 V DC) Switching function flow relay energized when flow is present and during the power-on delay time monitoring Switching function relay energized when temperature is exceeded temperature monitoring Switching function wire break relay de-energized in case of wire-break or short circuit monitoring

no

SN0150

Control monitor for flow sensors

VS3000/85...265VAC



Overload protection		no	
Reaction times			
Response time	[s]	< 3	
Software / programming			
Adjustment of the switch point		potentiometer	
Selection liquids / gases		wire bridge; on delivery: monitoring of liquids.; for monitoring of gases: link terminals 23 / 24.	
Switch point setting		potentiometer	
Temperature range	[°C]	080	
Repeatability switch point / measured value	[K]	4	
Operating conditions			
Ambient temperature	[°C]	-2060	
Note on ambient temperature		in case of sufficient free space for convection cooling	
Protection		IP 20	
Tests / approvals			
	years]	168	
	years]	168	
MTTF [years] [g]	168 252.5	
MTTF [
MTTF [Mechanical data Weight		252.5	
MTTF [Mechanical data Weight Housing	[g]	252.5 housing for DIN rail mounting	
MTTF [Mechanical data Weight Housing Dimensions	[g] [mm]	252.5 housing for DIN rail mounting 100 x 25 x 103.5	
MTTF [Mechanical data Weight Housing Dimensions Material	[g] [mm]	252.5 housing for DIN rail mounting 100 x 25 x 103.5	
MTTF Mechanical data Weight Housing Dimensions Material Displays / operating element	[g] [mm]	252.5 housing for DIN rail mounting 100 x 25 x 103.5 PBT Function Switching status LED, red	
MTTF Mechanical data Weight Housing Dimensions Material Displays / operating elemen Display	[g] [mm]	252.5 housing for DIN rail mounting 100 x 25 x 103.5 PBT	
MTTF Mechanical data Weight Housing Dimensions Material Displays / operating elemen Display Electrical connection	[g] [mm]	252.5 housing for DIN rail mounting 100 x 25 x 103.5 PBT Function Switching status LED, red	
MTTF Mechanical data Weight Housing Dimensions Material Displays / operating elemen Display	[g] [mm]	252.5 housing for DIN rail mounting 100 x 25 x 103.5 PBT Function Switching status LED, red	
MTTF Mechanical data Weight Housing Dimensions Material Displays / operating elemen Display Electrical connection	[g] [mm]	252.5 housing for DIN rail mounting 100 x 25 x 103.5 PBT Function 11 x LED Switching status LED, red Switching status LED, red	
MTTF Mechanical data Weight Housing Dimensions Material Displays / operating elemen Display Electrical connection Required protection	[g] [mm]	252.5 housing for DIN rail mounting 100 x 25 x 103.5 PBT Function 11 x LED Switching status LED, red Switching status LED, red	


SN0150

Control monitor for flow sensors

VS3000/85...265VAC

Electrical connection





Connection

1 =

2 =

3 =

4 =

5 =

Note

BN =

BU =

BK =

WH =

GY =

grey

