


# SM2601



## Magnetic-inductive flow meter

SMN21XGXFRKG/US-100



EC 1935/2004

### Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analog outputs: 1	
Measuring range	80...9600 gph	1.3...160 gpm
Process connection	threaded connection 2" NPT DN50	
<b>Application</b>		
System	gold-plated contacts	
Application	Totalizer function; empty pipe detection; for industrial applications	
Media	Conductive liquids; water; water-based media	
Note on media	conductivity: $\geq 20 \mu\text{S}/\text{cm}$ viscosity: $< 70 \text{ mm}^2/\text{s}$ (40 °C)	

# SM2601



## Magnetic-inductive flow meter

SMN21XGXRKG/US-100

Medium temperature	[°F]	14...194
Pressure rating	[bar]	16
Pressure rating	[psi]	232
MAWP (for applications according to CRN)	[bar]	16
<b>Electrical data</b>		
Operating voltage	[V]	18...32 DC; (to SELV/PELV)
Current consumption	[mA]	< 150
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	5
<b>Inputs / outputs</b>		
Number of inputs and outputs		Number of digital outputs: 2; Number of analog outputs: 1
<b>Inputs</b>		
Inputs		counter reset
<b>Outputs</b>		
Total number of outputs		2
Output signal		switching signal; analog signal; pulse signal; frequency signal; IO-Link; (configurable)
Electrical design		PNP/NPN
Number of digital outputs		2
Output function		normally open / closed; (configurable)
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	250; (per output)
Number of analog outputs		1
Analog current output	[mA]	4...20; (scalable)
Max. load	[Ω]	500
Analog voltage output	[V]	0...10; (scalable)
Min. load resistance	[Ω]	2000
Pulse output		flow rate meter
Short-circuit protection		yes
Type of short-circuit protection		yes (non-latching)
Overload protection		yes
Frequency of the output	[Hz]	0.1...10000
<b>Measuring/setting range</b>		
Measuring range	80...9600 gph	1.3...160 gpm
Display range	-11520...11520 gph	-190...190 gpm
Resolution	5 gph	0.1 gpm
Set point SP	130...9600 gph	2.1...160 gpm
Reset point rP	80...9550 gph	1.3...159.2 gpm
Analog start point ASP	0...7680 gph	0...128 gpm
Analog end point AEP	1920...9600 gph	32...160 gpm
Low flow cut-off LFC	< 240 gph	< 4 gpm
In steps of	5 gph	0.1 gpm

# SM2601



## Magnetic-inductive flow meter

SMN21XGXFRKG/US-100

Measuring dynamics	1:120
Volumetric flow quantity monitoring	
Pulse value	0.02...160 E06 gal
In steps of	0.02 gal
Pulse length [s]	0,008...2
Temperature monitoring	
Measuring range [°F]	-4...176
Display range [°F]	-40...212
Resolution [°F]	0.5
Set point SP [°F]	-2...176
Reset point rP [°F]	-3...175
Analog start point [°F]	-4...140
Analog end point [°F]	32...176
In steps of [°F]	0.5
<strong>Accuracy / deviations</strong>	
Flow monitoring	
Accuracy (in the measuring range)	± (0,8 % MW + 0,5 % MEW)
Repeatability	± 0,2% MEW
Temperature monitoring	
Temperature drift	± 0,0185 °F / K
Accuracy [K]	± 1 (77 °F; Q > 4 gpm)
<strong>Reaction times</strong>	
Flow monitoring	
Response time [s]	0.35; (dAP = 0)
Delay time programmable dS, dr [s]	0...50
Damping process value dAP [s]	0...5
Temperature monitoring	
Dynamic response T05 / T09 [s]	T09 = 3 (Q > 4 gpm)
<strong>Software / programming</strong>	
Parameter setting options	Flow monitoring; quantity meter; Preset counter; Temperature monitoring; hysteresis / window; normally open / closed; switching logic; current/voltage/frequency/pulse output; Start-up delay; display can be deactivated; Display unit; empty pipe detection
<strong>Interfaces</strong>	
Communication interface	IO-Link
Transmission type	COM2 (38,4 kBaud)
IO-Link revision	1.1
SDCI standard	IEC 61131-9 CDV
Profiles	Smart Sensor: Process Data Variable; Device Identification
SIO mode	yes
Required master port class	A
Process data analog	3
Process data binary	2

# SM2601



## Magnetic-inductive flow meter


SMN21XGXFRKG/US-100

Min. process cycle time	[ms]	5		
Supported DeviceIDs	Type of operation	DeviceID		
<b>Operating conditions</b>				
Ambient temperature	[°F]	14...140		
Storage temperature	[°F]	-13...176		
Protection		IP 65; IP 67		
<b>Tests / approvals</b>				
EMC	DIN EN 60947-5-9			
Shock resistance	DIN EN 60068-2-27	20 g (11 ms)		
Vibration resistance	DIN EN 60068-2-6	5 g (10...2000 Hz)		
MTTF	[years]	85		
UL approval	UL approval number	I008		
	File number UL	E174189		
Pressure equipment directive	sound engineering practice; can be used for group 2 fluids; group 1 fluids on request			
<b>Mechanical data</b>				
Weight	[g]	2643		
Material	stainless steel (1.4404 / 316L); stainless steel (1.4571/316Ti ); PEI; FKM; PBT-GF20; TPE-U			
Materials (wetted parts)	stainless steel (1.4404 / 316L); stainless steel (1.4571/316Ti ); PEEK; FKM			
Process connection	threaded connection 2" NPT DN50			
<b>Displays / operating elements</b>				
Display	Display unit	6 x LED, green (gpm, gph, gal, °F, 10 <sup>3</sup> , 1000 x 10 <sup>3</sup> )		
	Switching status	2 x LED, yellow		
	Measured values	alphanumeric display, 4-digit		
	Programming	alphanumeric display, 4-digit		
<b>Accessories</b>				
Items supplied	Label			
<b>Remarks</b>				
Remarks	MW = Measured value MEW = Final value of the measuring range			
Pack quantity	1 pcs.			
<b>Electrical connection</b>				
Connector: 1 x M12; coding: A; Contacts: gold-plated				
				

## Magnetic-inductive flow meter

SMN21XGXFRKG/US-100

### Connection



Colors to DIN EN 60947-5-2

OUT1: Switching output empty pipe detection

Switching output Volumetric flow quantity monitoring

Frequency output Volumetric flow quantity monitoring

Pulse output quantity meter

signal output Preset counter

IO-Link

OUT2: Switching output empty pipe detection

Switching output Volumetric flow quantity monitoring

Switching output Temperature monitoring

analog output Volumetric flow quantity monitoring

analog output Temperature monitoring

Input counter reset

Core colors :

BK = black


BN = brown

BU = blue

WH = white

### Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity