
SR0150

Control monitor for flow sensors

VS3000/24VDC







Application

Application		Flow monitoring; Temperature monitoring; Wire break monitoring
Electrical data		
Operating voltage tolerance	[%]	-2010
Operating voltage	[V]	24 DC
Current consumption	[mA]	90
Protection class		III
Reverse polarity protection		no
Power-on delay time	[s]	1080; (adjustable (fixed-value resistors terminals 22-23))
Number of channels		1
Outputs		
Performance in case of a fault		In case of undervoltage all relays are de-energized, the LED "LOW VOLTAGE/WIRE BREAK-RELAY" lights
Electrical design		Relay
Contact rating		4 A (250 V AC / 30 V DC)
Switching function flow monitoring		relay energized when flow is present and during the power-on delay time
Switching function temperature monitoring		relay energized when temperature is exceeded
Switching function wire break monitoring		relay de-energized in case of wire-break or short circuit
Short-circuit proof		no
Overload protection		no

SR0150

Control monitor for flow sensors





Reaction times			
Response time	[s]	< 3	
Software / programming			
Adjustment of the switch point		potentiometer	
Selection liquids / gases		wire bridge; on delivery: monitoring of liquids.; for monitoring of gases: link terminals 23 / 24.	
Switch point setting		potentiometer	
Temperature range	[°C]	080	
Repeatability switch point / measured value	[K]	4	
Operating conditions			
Ambient temperature	[°C]	-2060	
Note on ambient temperature		in case of sufficient free space for convection cooling	
Protection		IP 20	
Tests / approvals			
MTTF [y	/ears]	263	
MTTF () Mechanical data	/ears]	263	
	/ears]	263	
Mechanical data			
Mechanical data Weight		237.5	
Mechanical data Weight Housing	[g]	237.5 housing for DIN rail mounting	
Mechanical data Weight Housing Dimensions	[g] [mm]	237.5 housing for DIN rail mounting 100 x 25 x 103.5	
Mechanical data Weight Housing Dimensions Material	[g] [mm]	237.5 housing for DIN rail mounting 100 x 25 x 103.5 PBT Function 11 x LED	
Mechanical data Weight Housing Dimensions Material Displays / operating element	[g] [mm]	237.5 housing for DIN rail mounting 100 x 25 x 103.5 PBT Function 11 x LED Switching status LED, red	
Mechanical data Weight Housing Dimensions Material Displays / operating element Display	[g] [mm]	237.5 housing for DIN rail mounting 100 x 25 x 103.5 PBT Function 11 x LED	
Mechanical data Weight Housing Dimensions Material Displays / operating element Display	[g] [mm]	237.5 housing for DIN rail mounting 100 x 25 x 103.5 PBT Function 11 x LED Switching status LED, red LED, red LED, red	
Mechanical data Weight Housing Dimensions Material Displays / operating element Display Electrical connection Required protection	[g] [mm]	237.5 housing for DIN rail mounting 100 x 25 x 103.5 PBT Function 11 x LED Switching status LED, red	
Mechanical data Weight Housing Dimensions Material Displays / operating element Display Electrical connection Required protection Remarks	[g] [mm]	237.5 housing for DIN rail mounting $100 \times 25 \times 103.5$ PBT Function $11 \times \text{LED}$ Switching status LED, red Switching status LED, red miniature fuse to IEC60127-2 sheet 1; $\leq 5 \text{ A}$; fast acting	
Mechanical data Weight Housing Dimensions Material Displays / operating element Display Electrical connection Required protection	[g] [mm]	237.5 housing for DIN rail mounting 100 x 25 x 103.5 PBT Function 11 x LED Switching status LED, red LED, red LED, red	

SR0150

Control monitor for flow sensors


VS3000/24VDC



Electrical connection

Combicon connector:

Connection



1 = Flow monitoring2 = Wire break monitoring3 = Temperature monitoring

4 = External resistor to set the power-on delay time

5 = Link to monitor gaseous media

Note miniature fuse to IEC60127-2 sheet $1 \le 5$ A fast acting

Core colors:

BN = brown
BU = blue
BK = black
WH = white
GY = grey