


## Connecting cable with socket

ADOGH040MSN0002A04

Article no longer available - archive entry

Alternative articles: ENC01A

When selecting an alternative article and accessories please note that technical data may differ!



## Application

Application	Ex zone 1
-------------	-----------

## Electrical data

Operating voltage	[V]	< 15 DC
-------------------	-----	---------

## Operating conditions

Ambient temperature	[°C]	-25...90
---------------------	------	----------

Protection	IP 67
------------	-------

## Safety classification

Max. internal capacitance	[nF]	0.196
---------------------------	------	-------

Max. internal inductance	[μH]	4
--------------------------	------	---

## Mechanical data

Dimensions	[mm]	15 x 15 x 43
------------	------	--------------

Materials	TPU blue
-----------	----------

Moulded-body material	TPU, blue
-----------------------	-----------

Material nut	brass, nickel-plated
--------------	----------------------

## Remarks

Remarks	When using sockets in hazardous areas (ATEX) there are special requirements regarding wiring.
	The requirements of the applicable installation regulations must be absolutely adhered to by the user on his own responsibility.

Pack quantity	1 pcs.
---------------	--------

# E10357



## Connecting cable with socket

ADOGH040MSN0002A04

### Electrical connection


Cable: 2 m, PUR / PVC, blue, Ø 5 mm; 4 x 0.34 mm² (42 x Ø 0.1 mm )

### Electrical connection - socket

Connector: 1 x M12, straight; coding: A; Moulded body: TPU, blue; Locking: brass, nickel-plated; Tightening torque: 0.5 Nm



### Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue
WH =	white