


E80406



RFID tag

ID-TAG/7.5X1.0/06



Application

Operating temperature (active)	[°C]	-40...85
Peak temperature (passive)	[°C]	85

Electrical data

Operating frequency	[MHz]	13,56
Memory size	[bit]	896
Chip type		ICODE SLIX
Number of blocks		28
Block size	[Byte]	4
Unique Identification Number (UID)	[Byte]	8
RFID standard		ISO 15693

Operating conditions

Ambient temperature	[°C]	-40...85
Storage temperature	[°C]	-40...85
Protection		IP 68

Tests / approvals

Shock resistance	DIN IEC 68-2-27	40 g (18 ms)
Vibration resistance	DIN IEC 68-2-6	10 g (10...2000 Hz)

Mechanical data

Weight	[g]	2.1
Dimensions	[mm]	Ø 7.5 / L = 1
Materials		housing: Epoxydharz

Remarks

Pack quantity		10 pcs.
---------------	--	---------

E80406



RFID tag

ID-TAG/7.5X1.0/06

Other data

Reading distance when mounted on non-metal (mm)

ANT410 / DTI410	10
ANT411 / DTI411	10
ANT420 / DTI420 / DTM424 / DTI424 / DTM426	10
ANT421 / DTI421 / DTM425 / DTI425 / DTM427	20
ANT430 / DTI430 / DTM434 / DTI434 / DTM436	15
ANT431 / DTI431 / DTM435 / DTI435 / DTM437	25
ANT513 / DTI513 / DTC510	30
ANT515 / DTI515 / ANT516 / DTI516	10
ANT600 / DTI600	-