


Inductive sensor

IDC2050BABOA/LS-100K

Article no longer available - archive entry



Product characteristics

Output function		normally open
Sensing range	[mm]	50
Housing		rectangular
Dimensions	[mm]	92 x 80 x 40

Electrical data

Operating voltage	[V]	20...250 AC/DC
Protection class		I
Reverse polarity protection		no

Outputs

Output function		normally open
Max. voltage drop switching output DC	[V]	6
Max. voltage drop switching output AC	[V]	6.5
Minimum load current	[mA]	5
Max. leakage current	[mA]	0.8
Permanent current rating of switching output AC	[mA]	250; (350 (...50 °C))
Permanent current rating of switching output DC	[mA]	100
Short-time current rating of switching output	[mA]	2200; (20 ms / 0,5 Hz)
Switching frequency AC	[Hz]	25
Switching frequency DC	[Hz]	25

**Inductive sensor**

IDC2050BABOA/LS-100K

Short-circuit protection	no	
Overload protection	no	
Detection zone		
Sensing range	[mm]	50
Operating distance	[mm]	0...40.5; (mounted flush with mild steel (ST37))
Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.85 / brass: 0.48 / aluminium: 0.46 / copper: 0.38	
Hysteresis	[% of Sr]	3...20
Switch point drift	[% of Sr]	-15...15
Operating conditions		
Ambient temperature	[°C]	-25...70
Protection	IP 67	
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing	rectangular	
Mounting	flush mountable	
Dimensions	[mm]	92 x 80 x 40
Materials	PPE modified	
Displays / operating elements		
Display	switching status	1 x LED, red
Accessories		
Items supplied	screwdriver: 1	
Remarks		
Pack quantity	1 pcs.	



Inductive sensor

IDC2050BABOA/LS-100K

Electrical connection - plug

Connector: 1 x 1/2"; coding: C

