


Inductive sensor

IGA3005LBNOG/BS-201-ANO

Article no longer available - archive entry



Product characteristics

Electrical design	NPN
Output function	normally closed
Sensing range [mm]	5
Housing	threaded type
Dimensions [mm]	M18 x 1

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	7; (24 V)
Reverse polarity protection	no

Outputs

Electrical design	NPN
Output function	normally closed
Max. voltage drop switching output DC [V]	1
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	200
Short-circuit protection	no
Overload protection	no

Detection zone

Sensing range [mm]	5
Real sensing range Sr [mm]	5 ± 10 %
Operating distance [mm]	0...4.05



Inductive sensor

IGA3005LBNOG/BS-201-ANO

Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.4 / copper: 0.3	
Hysteresis	[% of Sr]	3...15	
Switch point drift	[% of Sr]	-10...10	
Operating conditions			
Ambient temperature		[°C]	-25...80
Protection		IP 67	
Mechanical data			
Housing		threaded type	
Mounting		flush mountable	
Dimensions		[mm]	M18 x 1
Thread designation		M18 x 1	
Materials		brass nickel-plated; PBT	
Displays / operating elements			
Display		switching status	1 x LED, yellow
Accessories			
Items supplied		lock nuts: 2	
Remarks			
Pack quantity		1 pcs.	
Electrical connection - plug			
Connector: 1 x M18; coding: A			
			

Connection

