




Inductive sensor

IFK3007-BPKG/M/60V/US-104-DPS



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	7
Housing	threaded type
Dimensions [mm]	M12 x 1 / L = 70

Application

Special feature	Gold-plated contacts; Increased sensing range
Application	Use in mobile and harsh applications

Electrical data

Operating voltage [V]	10...60 DC
Current consumption [mA]	< 10
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	300
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Sensing range [mm]	7
Real sensing range Sr [mm]	$7 \pm 10 \%$
Operating distance [mm]	0...5.67
Increased sensing range	yes



Inductive sensor

IFK3007-BPKG/M/60V/US-104-DPS

Accuracy / deviations				
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.5 / copper: 0.4		
Hysteresis	[% of Sr]	1...20		
Switch point drift	[% of Sr]	-10...10		
Operating conditions				
Ambient temperature		[°C]	-40...85	
Protection		IP 67; IP 69K		
Tests / approvals				
EMC		automotive area		
		noise emission and noise interference: ECE R10		E1 type approval
		noise immunity according to DIN ISO 11452-2		100 V/m
		conducted interference in 24 V networks to ISO 7637-2: 2004 (pulse 1 to 4) and ISO16750-2: 2012 (load dump)		
		pulse		1 2a 2b 3a 3b 4 Load dump
		severity level		III III III III III Test A
		failure criterion		C A C A A C C
		EN 61000-4-2 ESD		4 kV CD / 8 kV AD
		EN 61000-4-3 HF radiated		10 V/m
		EN 61000-4-4 Burst		2 kV
		EN 61000-4-5 Surge		0,5 kV mains line to line
		EN 61000-4-6 HF conducted		10 V
		EN 55011		class B
Vibration resistance		EN 60068-2-6 Fc		20 g (10...3000 Hz) / -20...50 °C
				50 sweep cycles, 1 octave per minute, in 3 axes
Shock resistance		EN 60068-2-27 Ea		100 g 11 ms half-sine; 3 shocks each in every direction of the 3 coordinate axes / -40...85 °C
Continuous shock resistance		EN 60068-2-27		40 g 6 ms; 4000 shocks each in every direction of the 3 coordinate axes / -20...50 °C
Fast temperature change		EN 60068-2-14 Na		TA = -40 °C; TB = 85 °C; t1 = 30 min; t2 = < 10 s; 50 cycles
Salt spray test		EN 60068-2-52 Kb		severity level 5 (4 test cycles)
MTTF		[years]	666	
UL approval		Ta		0...40 °C
		Enclosure type		Type 1
		power supply		Hazardous voltage
		File number UL		E174191
Mechanical data				
Weight		[g]	29.8	
Housing		threaded type		
Mounting		non-flush mountable		
Dimensions		[mm]	M12 x 1 / L = 70	
Thread designation		M12 x 1		
Materials		housing: stainless steel; sensing face: LCP natural; LED window: PEI; lock nuts: brass		

IFM206



Inductive sensor

IFK3007-BPKG/M/60V/US-104-DPS

Displays / operating elements

Display	switching status	4 x 90° LED, yellow
---------	------------------	---------------------

Accessories


Items supplied	lock nuts: 2
----------------	--------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

