


Inductive sensor

IIC2010-AROG/ 3mPPU

Article no longer available - archive entry



Product characteristics

Electrical design	PNP/NPN
Output function	normally open
Sensing range [mm]	10
Housing	threaded type
Dimensions [mm]	M30 x 1.5

Electrical data

Operating voltage [V]	10...36 DC
Reverse polarity protection	no

Outputs

Electrical design	PNP/NPN
Output function	normally open
Max. voltage drop switching output DC [V]	4.6
Minimum load current [mA]	5
Max. leakage current [mA]	0.4
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	30
Short-circuit protection	no
Overload protection	no

Detection zone


Sensing range [mm]	10
Real sensing range S_r [mm]	$10 \pm 10 \%$
Operating distance [mm]	0...8.1



Inductive sensor

IIC2010-AROG/ 3mPPU

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.4 / copper: 0.3
Hysteresis	[% of Sr]	
Switch point drift	[% of Sr]	
		1...15
		-10...10
Operating conditions		
Ambient temperature		[-°C]
Protection		
		-25...80
		IP 67
Mechanical data		
Housing		
Mounting		threaded type
Dimensions		flush mountable
Thread designation		M30 x 1.5
Materials		M30 x 1.5
		housing: PTFE; cable sleeve: PBT
Displays / operating elements		
Display		switching status
		1 x LED, yellow
Accessories		
Items supplied		lock nuts: 2
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 3 m, PUR; 2 x 0.5 mm²		
Connection		



BK = Core colours :
black