



Through-beam sensor receiver

OLE-FNKG/LS-400

Article no longer available - archive entry

Alternative articles: O5E502 + E21122

When selecting an alternative article and accessories please note that technical data may differ!

No scale drawing available

Product characteristics

Housing	rectangular
---------	-------------

Application

Function principle	Through-beam sensor
--------------------	---------------------

Electrical data

Operating voltage	[V]	10...36 DC
-------------------	-----	------------

Current consumption	[mA]	< 30
---------------------	------	------

Protection class	II
------------------	----

Reverse polarity protection	yes
-----------------------------	-----

Overtoltage protection	yes
------------------------	-----

Outputs

Electrical design	NPN
-------------------	-----

Output function	light-on/dark-on mode; (parameterisable)
-----------------	--

Max. voltage drop switching output DC	[V]	2.5
---------------------------------------	-----	-----

Permanent current rating of switching output DC	[mA]	100; (200 (...50 °C))
---	------	-----------------------

Switching frequency DC	[Hz]	500
------------------------	------	-----

Short-circuit protection	yes
--------------------------	-----

Type of short-circuit protection	pulsed
----------------------------------	--------

Detection zone

Transmitter / receiver	receiver
------------------------	----------

Range	[m]	< 25
-------	-----	------

OL5042



Through-beam sensor receiver

OLE-FNKG/LS-400

Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing		rectangular
Dimensions	[mm]	75 x 27 x 62
Materials		PBT
Lens material		PMMA
Displays / operating elements		
Display	switching status	1 x LED, yellow
	operation	1 x LED, green
	function	1 x LED, red
Remarks		
Pack quantity		1 pcs.
Electrical connection		

Connector: 1 x 7/8" / M12; coding: A



Connection

