

OYA0610-50-2-12-P-1

Technical drawing of a 12V/20Ah battery, showing front, side, and detail views with dimensions in mm.

Front View (Left): Shows the battery terminals. The top terminal is labeled 'T' and the bottom terminal is labeled '1'. The battery has a width of 28 mm and a height of 30 mm.

Side View (Top): Shows the battery's profile. The total length is labeled 'L'. The distance from the top terminal to the center of the battery is 11 mm. The distance from the bottom terminal to the center is 29.5 mm. The total height is 61.5 mm. The bottom terminal is labeled 'M12x1'.

Side View (Bottom): Shows the battery's profile. The total length is labeled 'L'. The distance from the top terminal to the center is 11 mm. The distance from the bottom terminal to the center is 29.5 mm. The total height is 61.5 mm. The bottom terminal is labeled 'M12x1'.

Detail Views (Right):

- Top Terminal Detail:** Shows the terminal with a width of 10 mm and a height of 40 mm. The distance from the center to the edge is 20 mm.
- Bottom Terminal Detail:** Shows the terminal with a width of 10 mm and a height of 1.5 mm. The distance from the center to the edge is 20 mm.
- Terminal Mounting Detail:** Shows the terminal with a width of 10 mm and a height of 1.5 mm. The distance from the center to the edge is 20 mm.
- Terminal Mounting Detail:** Shows the terminal with a width of 10 mm and a height of 1.5 mm. The distance from the center to the edge is 20 mm.

- | | |
|---|---------------------------------------|
| T | transmitter |
| R | receiver |
| 1 | LED three-colour red / green / orange |
| 2 | LED yellow |
| 3 | LED 2-colour red/green |



Type of light	infrared light
Electrical design	PNP
Protection	IP 65; IP 67

Protective function	access prevention bodies or parts of bodies
---------------------	---



Safety light curtain

OYA0610-50-2-12-P-1

Electrical data		
Operating voltage tolerance	[%]	20
Operating voltage	[V]	24 DC
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	< 2
Type of light		infrared light
Wave length	[nm]	950
Receiver		
Current consumption	[mA]	83
Transmitter		
Current consumption	[mA]	42
Outputs		
Electrical design		PNP
Number of OSSD outputs		2
Max. current load per OSSD output	[mA]	400; (24 V)
Short-circuit protection		yes
Detection zone		
Protected area height	[mm]	610
Resolution (detection capacity d)	[mm]	50
Protection area width (low light intensity)	[m]	0...4
Protection area width (high light intensity)	[m]	3...12
Response times		
Response time	[ms]	6
Operating conditions		
Applications		class C to EN 60654-1 weatherproof application
Ambient temperature	[°C]	-10...55
Storage temperature	[°C]	-20...70
Max. relative air humidity	[%]	95
Protection		IP 65; IP 67
Tests / approvals		
EMC	IEC 61496-1	
Shock resistance	IEC 61496-1	
Vibration resistance	IEC 61496-1	
Safety classification		
ESPE type (IEC 61496-1)		2
Complies with the requirements		ISO 13849-1: 2015 category 2, PL c IEC 62061 SIL 1
Mission time TM	[h]	175200
PFH	[1/h]	2,8E-08

OY074S



Safety light curtain

OYA0610-50-2-12-P-1

Mechanical data		
Weight	[g]	2365
Dimensions	[mm]	663 x 28 x 30
Materials		housing: aluminium; front pane: PC
Length L	[mm]	663

Displays / operating elements		
Display	transmitter	1 x LED
	receiver	2 x LED

Accessories		
Items supplied		mounting bracket: 4
		slot nuts: 4
		Nuts

Remarks	
Pack quantity	1 pcs.

Electrical connection - receiver

Connector: 1 x M12; coding: A; Maximum cable length: 100 m; for wire cross-section 0.34 mm²



Connection



Safety light curtain

OYA0610-50-2-12-P-1

Electrical connection - transmitter

Connector: 1 x M12; coding: A



Connection

