


SM7001

Magnetic-inductive flow meter

SMR34GGXFRKG/US-100



CE CRN cULus DNV EC 1935/2004 IO-Link UK CA
LISTED DNV.COM/AF

Product characteristics	
Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1
Measuring range	3...792 gph 0.06...13.2 gpm
Process connection	threaded connection G 3/4 DN20 flat seal
Application	
Special feature	Gold-plated contacts
Application	totaliser function; for industrial applications
Installation	connection to pipe by means of an adapter
Media	conductive liquids; water; hydrous media
Note on media	conductivity: $\geq 20 \mu\text{S}/\text{cm}$ viscosity: $< 70 \text{ mm}^2/\text{s}$ (40 °C)
Medium temperature	[°F] 14...158
Pressure rating	[bar] 16
Pressure rating	[psi] 232
MAWP (for applications according to CRN)	[bar] 11.2
Electrical data	
Operating voltage	[V] 18...30 DC; (to SELV/PELV)
Current consumption	[mA] 95; (24 V)
Protection class	III
Reverse polarity protection	yes
Power-on delay time	[s] 5
Inputs / outputs	
Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1
Inputs	
Inputs	counter reset
Outputs	
Total number of outputs	2

SM7001

Magnetic-inductive flow meter

SMR34GGXFRKG/US-100



Output signal		switching signal; analogue signal; pulse signal; IO-Link; (configurable)
Electrical design		PNP/NPN
Number of digital outputs		2
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	200
Number of analogue outputs		1
Analogue current output	[mA]	4...20; (scalable)
Max. load	[Ω]	500
Analogue voltage output	[V]	0...10; (scalable)
Min. load resistance	[Ω]	2000
Pulse output		flow rate meter
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Measuring/setting range		
Measuring range		3...792 gph 0.06...13.2 gpm
Display range		-951...951 gph -15.84...15.84 gpm
Resolution		1 gph 0.02 gpm
Set point SP		7...792 gph 0.12...13.2 gpm
Reset point rP		3...788 gph 0.06...13.14 gpm
Analogue start point ASP		0...636 gph 0...10.6 gpm
Analogue end point AEP		156...792 gph 2.6...13.2 gpm
In steps of		1 gph 0.02 gpm
Volumetric flow quantity monitoring		
Pulse value		0.01...99 990 000 gal
Pulse length	[s]	0,005...2
Temperature monitoring		
Measuring range	[°F]	-4...176
Resolution	[°F]	0.5
Set point SP	[°F]	-2.5...176
Reset point rP	[°F]	-3.5...175
Analogue start point	[°F]	-4...140.5
Analogue end point	[°F]	31.5...176
In steps of	[°F]	0.5
Accuracy / deviations		
Flow monitoring		
Accuracy (in the measuring range)		± (0,8 % MW + 0,5 % MEW)
Repeatability		± 0,2% MEW
Temperature monitoring		
Accuracy	[K]	± 2,5 (Q > 0,26 gpm)

SM7001

Magnetic-inductive flow meter

SMR34GGXFRKG/US-100



Response times		
Flow monitoring		
Response time	[s]	0.15; (dAP = 0, T19)
Delay time programmable dS, dr	[s]	0...50
Damping process value dAP	[s]	0...5
Temperature monitoring		
Dynamic response T05 / T09	[s]	T09 = 20 (Q > 0,26 gpm)
Software / programming		
Parameter setting options		Flow monitoring; quantity meter; Preset counter; Temperature monitoring; hysteresis / window; normally open / normally closed; switching logic; current/voltage/pulse output; start-up delay; display can be deactivated; Display unit
Interfaces		
Communication interface		IO-Link
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.1
SDCI standard		IEC 61131-9
Profiles		Smart Sensor: Process Data Variable; Device Identification, Device Diagnosis
SIO mode		yes
Required master port type		A
Process data analogue		3
Process data binary		2
Min. process cycle time	[ms]	5
Supported DeviceIDs	Type of operation	DeviceID
	default	573
Operating conditions		
Ambient temperature	[°F]	14...140
Storage temperature	[°F]	-13...176
Protection		IP 67
Tests / approvals		
EMC		DIN EN 60947-5-9
Shock resistance		DIN IEC 68-2-27
Vibration resistance		DIN IEC 68-2-6
MTTF	[years]	145
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request
Mechanical data		
Weight	[g]	586
Materials		stainless steel (316L/1.4404); PBT-GF20; PC; FKM; TPE
Materials (wetted parts)		stainless steel (316L/1.4404); PEEK; FKM
Process connection		threaded connection G 3/4 DN20 flat seal

SM7001



Magnetic-inductive flow meter

SMR34GGXFRKG/US-100

Displays / operating elements	
Display	Display unit
	switching status
	measured values
	programming

Remarks


Remarks	MW = measured value MEW = Final value of the measuring range
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



OUT1: colours to DIN EN 60947-5-2
switching output volumetric flow quantity monitoring
Pulse output quantity meter
signal output Preset counter
IO-Link

OUT2: switching output volumetric flow quantity monitoring
switching output Temperature monitoring
analogue output volumetric flow quantity monitoring
analogue output Temperature monitoring
input counter reset

Core colours :

BK = black

BN = brown

BU = blue

WH = white

SM7001




Magnetic-inductive flow meter

SMR34GGXFRKG/US-100

Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity