

SN0100




Control monitor for flow sensors

VS0200/230VAC

Article no longer available - archive entry

Alternative articles: SN0150

When selecting an alternative article and accessories please note that technical data may differ!



1 mounting on DIN rail



Application

Application Flow monitoring

Electrical data

Operating voltage tolerance [%]	-10...10
Operating voltage [V]	< 230 AC
Max. power consumption [VA]	3
Power-on delay time [s]	30
Number of channels	1

Outputs

Electrical design	relay
Contact rating	4 A, 250 V AC
Switching function flow monitoring	relay energised when flow is present

Software / programming

Adjustment of the switch point	potentiometer
Selection liquids / gases	slide switch

Operating conditions

Ambient temperature [°C]	0...60
Protection	IP 40
Protection rating terminals	IP 20

SN0100



Control monitor for flow sensors

VS0200/230VAC

Mechanical data	
Housing	housing for DIN rail mounting
Dimensions [mm]	75 x 55 x 110
Materials	plastics


Displays / operating elements		
Display	function	11 x LED

Remarks	
Pack quantity	1 pcs.

Electrical connection

terminals: 16 x ...2.5 mm²

Connection



- 1: Relais Flow monitoring
Core colours :
- BN = brown
 - BU = blue
 - BK = black
 - WH = white
 - GY = grey