




Pressure transmitter

PT-1,6-AFG14-A-ZVG/US



1 Sealing



Product characteristics

Number of inputs and outputs	Number of analogue outputs: 1			
Measuring range	0...1.6 bar	0...1600 mbar	0...23.2 psi	0...160 kPa
Process connection	threaded connection G 1/4 external thread (DIN EN ISO 1179-2)			

Application

Application	for industrial applications		
Media	liquids and gases		
Medium temperature [°C]	0...80		
Min. bursting pressure	10 bar	145 psi	1000 kPa
Pressure rating	3.2 bar	46 psi	320 kPa
Type of pressure	absolute pressure		

Electrical data

Operating voltage [V]	8...30 DC
Min. insulation resistance [MΩ]	100; (500 V DC)
Protection class	III
Reverse polarity protection	yes

Inputs / outputs

Number of inputs and outputs	Number of analogue outputs: 1
------------------------------	-------------------------------

Outputs

Total number of outputs	1
Output signal	analogue signal
Number of analogue outputs	1
Analogue current output [mA]	4...20
Max. load [Ω]	800; (U _b = 24 V; (U _b - 8 V) / 20 mA)
Short-circuit proof	yes

Measuring/setting range

Measuring range	0...1.6 bar	0...1600 mbar	0...23.2 psi	0...160 kPa
-----------------	-------------	---------------	--------------	-------------



Pressure transmitter

PT-1,6-AFG14-A-ZVG/US

Accuracy / deviations		
Repeatability	[% of the span]	< ± 0,1; (with temperature fluctuations < 10 K)
Characteristics deviation	[% of the span]	< ± 1,0; (incl. zero point and span error, non-linearity, hysteresis)
Linearity deviation	[% of the span]	< ± 0,5 (BFSL) / < ± 1,0 (LS)
Long-term stability	[% of the span]	< ± 0,1; (per year)
Temperature coefficient zero point	[% of the span / 10 K]	< ± 0,2; (0...80 °C)
Temperature coefficient span	[% of the span / 10 K]	< ± 0,2; (0...80 °C)
Response times		
Step response time analogue output	[ms]	4
Operating conditions		
Ambient temperature	[°C]	0...80
Storage temperature	[°C]	-20...80
Protection		IP 67
Tests / approvals		
EMC	DIN EN 61326-1	
Shock resistance	DIN EN 60068-2-27	500 g (1 ms)
Vibration resistance	DIN EN 60068-2-6	10 g (10...2000 Hz)
MTTF	[years]	815
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	
Mechanical data		
Weight	[g]	118
Materials	stainless steel (316L/1.4404); HNBR; PA	
Materials (wetted parts)	stainless steel (316L/1.4404)	
Min. pressure cycles	10 million	
Tightening torque	[Nm]	25...35; (recommended tightening torque; depends on lubrication, seal and pressure rating)
Process connection	threaded connection G 1/4 external thread (DIN EN ISO 1179-2)	
Process connection sealing	NBR (DIN EN ISO 1179-2)	
Fill fluid for pressure transmission	synthetic oil	
Restrictor element integrated	no	
Remarks		
Remarks	BFSL = Best Fit Straight Line	
	LS = limit value setting	
Pack quantity	1 pcs.	

PT0517



Pressure transmitter


PT-1,6-AFG14-A-ZVG/US

Electrical connection

Connector: 1 x M12; coding: A



Connection



OUT	analogue output colours to DIN EN 60947-5-2
BN =	brown
WH =	white