

AC1333

AS-Interface PLC


ControllerE M4 1Master RS232



Article no longer available - archive entry

Alternative articles: AC1401 or AC1403

When selecting an alternative article and accessories please note that technical data may differ!



Application

Application	decentralised controller
-------------	--------------------------

Electrical data

Operating voltage	[V]	24 DC
Insulation rating	[V]	500
Current consumption	[mA]	< 500
Max. current consumption from AS-i	[mA]	10
Max. power consumption	[VA]	10
Number of AS-i masters		1
Electrical separation		yes

Interfaces

Communication interface	RS232
RS232	
Number of R232 interfaces	1

AC1333



AS-Interface PLC

ControllerE M4 1Master RS232

Transmission rate	9600...115200 Baud
Connector type	RJ11
Usage type	programming
Note on interfaces	electrically isolated

Operating conditions

Ambient temperature	[°C]	0...60
Storage temperature	[°C]	-20...70
Protection		IP 20

AS-i classification

AS-i version	2.11; 3.0
AS-i master profile	M4

Mechanical data

Weight	[g]	530.5
Housing		housing for DIN rail mounting
Materials		aluminium; steel sheet galvanised

Displays / operating elements

Display	function	1 x LED, red
		2 x LED, green
		2 x LED, yellow
		full graphic LCD display

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connection	
------------	--

