
E20977

Fibre optic through-beam sensor

FE-50-V-V-M5/16/2M

Article no longer available - archive entry



Application		
Function principle		Through-beam sensor
Detection zone		
Range with fibre-optic amplifier type		ODF; OMF
ODF		
Range of fibre optics	[mm]	4
OMF		
Range of fibre optics	[mm]	1000
Operating conditions		
Ambient temperature	[°C]	-58...315
Mechanical data		
Version of sensing head		straight
Total length	[mm]	2000
Min. bending radius	[mm]	19
Fibre material		glass
Fibre head material		stainless steel (1.4305 / 303)
Fibre sheath material		stainless steel (1.4305 / 303)

E20977

Fibre optic through-beam sensor

FE-50-V-V-M5/16/2M

Remarks	
Pack quantity	1 pcs.