




## Inductive full-metal sensor

IFG3003BBPKG/AM/US-104



## Product characteristics

|                    |               |
|--------------------|---------------|
| Electrical design  | PNP           |
| Output function    | normally open |
| Sensing range [mm] | 3             |
| Housing            | cylindrical   |
| Dimensions [mm]    | Ø 12 / L = 60 |

## Application

|                         |                                                                   |
|-------------------------|-------------------------------------------------------------------|
| Special feature         | Gold-plated contacts; Increased sensing range; Full-metal housing |
| Application             | Use in wet areas and in the food and beverage industry            |
| Pressure rating [bar]   | 50                                                                |
| Note on pressure rating | sensing face                                                      |

## Electrical data

|                             |            |
|-----------------------------|------------|
| Operating voltage [V]       | 10...36 DC |
| Current consumption [mA]    | < 20       |
| Protection class            | III        |
| Reverse polarity protection | yes        |

## Outputs

|                                                      |               |
|------------------------------------------------------|---------------|
| Electrical design                                    | PNP           |
| Output function                                      | normally open |
| Max. voltage drop switching output DC [V]            | 2.5           |
| Permanent current rating of switching output DC [mA] | 100           |
| Switching frequency DC [Hz]                          | 100           |
| Short-circuit protection                             | yes           |
| Type of short-circuit protection                     | pulsed        |
| Overload protection                                  | yes           |

## Detection zone

|                         |         |
|-------------------------|---------|
| Sensing range [mm]      | 3       |
| Operating distance [mm] | 0...2.4 |
| Increased sensing range | yes     |



## Inductive full-metal sensor

IFG3003BBPKG/AM/US-104

| Accuracy / deviations                                                                          |                           |                                                                                                                                                |
|------------------------------------------------------------------------------------------------|---------------------------|------------------------------------------------------------------------------------------------------------------------------------------------|
| Correction factor                                                                              |                           | steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.1                                                                    |
| Hysteresis                                                                                     | [% of Sr]                 | 1...20                                                                                                                                         |
| Operating conditions                                                                           |                           |                                                                                                                                                |
| Ambient temperature                                                                            |                           | [°C] 0...100                                                                                                                                   |
| Protection                                                                                     |                           | IP 68; IP 69K                                                                                                                                  |
| Tests / approvals                                                                              |                           |                                                                                                                                                |
| EMC                                                                                            | EN 61000-4-2 ESD          | 4 kV CD / 8 kV AD                                                                                                                              |
|                                                                                                | EN 61000-4-3 HF radiated  | 10 V/m                                                                                                                                         |
|                                                                                                | EN 61000-4-4 Burst        | 2 kV                                                                                                                                           |
|                                                                                                | EN 61000-4-6 HF conducted | 10 V                                                                                                                                           |
|                                                                                                | EN 55011 emission         | class B                                                                                                                                        |
| Impact resistance                                                                              |                           | 1 J                                                                                                                                            |
| MTTF                                                                                           | [years]                   | 1258                                                                                                                                           |
| UL approval                                                                                    | Ta                        | -25...70 °C                                                                                                                                    |
|                                                                                                | Enclosure type            | Type 1                                                                                                                                         |
|                                                                                                | power supply              | Limited Voltage/Current                                                                                                                        |
|                                                                                                | UL Approval no.           | A012                                                                                                                                           |
|                                                                                                | File number UL            | E174191                                                                                                                                        |
| Mechanical data                                                                                |                           |                                                                                                                                                |
| Weight                                                                                         | [g]                       | 19.645                                                                                                                                         |
| Housing                                                                                        |                           | cylindrical                                                                                                                                    |
| Mounting                                                                                       |                           | flush mountable                                                                                                                                |
| Dimensions                                                                                     | [mm]                      | Ø 12 / L = 60                                                                                                                                  |
| Materials                                                                                      |                           | housing: stainless steel (316L/1.4404); sensing face: stainless steel (316L/1.4404); LED window: PEI; lock nuts: stainless steel (316L/1.4404) |
| Full-metal housing                                                                             |                           | yes                                                                                                                                            |
| Displays / operating elements                                                                  |                           |                                                                                                                                                |
| Display                                                                                        | switching status          | 4 x 90° LED, yellow                                                                                                                            |
| Remarks                                                                                        |                           |                                                                                                                                                |
| Pack quantity                                                                                  |                           | 1 pcs.                                                                                                                                         |
| Electrical connection - plug                                                                   |                           |                                                                                                                                                |
| Connector: 1 x M12; coding: A; Contacts: gold-plated                                           |                           |                                                                                                                                                |
| <div></div> |                           |                                                                                                                                                |

# IFT243

## Inductive full-metal sensor

IFG3003BBPKG/AM/US-104



### Connection

