

IE5163




Inductive sensor

IE-3001-ANOG/6M

Article no longer available - archive entry

Discontinuation date: 31.03.2019



Product characteristics

Electrical design	NPN
Output function	normally open
Sensing range [mm]	1
Housing	threaded type
Dimensions [mm]	M8 x 1 / L = 50

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	15; (24 V)
Protection class	III
Reverse polarity protection	no

Outputs

Electrical design	NPN
Output function	normally open
Max. voltage drop switching output DC [V]	1
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	1000
Short-circuit protection	no
Overload protection	no

Detection zone

Sensing range [mm]	1
Real sensing range S_r [mm]	$1 \pm 10\%$
Operating distance [mm]	0...0.8

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis [% of S_r]	1...15
Switch point drift [% of S_r]	-10...10


IE5163



Inductive sensor

IE-3001-ANOG/6M

Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
MTTF	[years]	2673
Mechanical data		
Housing		threaded type
Mounting		flush mountable
Dimensions	[mm]	M8 x 1 / L = 50
Thread designation		M8 x 1
Materials		PBT
Displays / operating elements		
Display	switching status	1 x LED, yellow
Accessories		
Items supplied		lock nuts: 2
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 6 m, PVC; 3 x 0.14 mm ²		
Connection		



Core colours :

BN = brown
BU = blue
BK = black

Article no longer available - archive entry

Discontinuation date: 31.03.2019