

# AC2210




## AS-Interface control cabinet module

Modul aktiv, 4E 200mA/4AT PNP

Article no longer available - archive entry

Alternative article: AC2257 When selecting an alternative article and accessories please note that technical data may differ! – When selecting an alternative article and accessories please note that technical data may differ!



1 addressing socket



### Electrical data

Operating voltage	[V]	26.5...31.6 DC
Current consumption	[mA]	< 235
Max. current load total	[A]	6
Integrated watchdog		yes

### Inputs / outputs

Number of inputs and outputs	Number of digital inputs: 4; Number of digital outputs: 4
------------------------------	---

### Inputs


Number of digital inputs	4; (bidirectional)
Input circuit of digital inputs	PNP
Sensor supply of the inputs	AS-i
Voltage supply	[V] 20...30
Max. total current rating of inputs	[mA] 200
Input current High	[mA] > 5
Input current Low	[mA] < 1.5
Min. switching level high signal	[V] 10
Digital inputs protected against short circuits	yes



## AS-Interface control cabinet module

Modul aktiv, 4E 200mA/4AT PNP

Outputs		
Electrical design	AS-i	
Number of digital outputs	4	
Circuit	PNP	
Voltage range DC [V]	10...30; (to PELV)	
Max. current load per output [mA]	2000	
Short-circuit proof	yes	
Electrically separated	yes	
Operating conditions		
Ambient temperature [°C]	-25...80	
Protection	IP 20	
Tests / approvals		
EMC	EN 50295	
AS-i classification		
AS-i profile	S-7.0	
AS-i I/O configuration [hex]	7	
AS-i ID code [hex]	0	
AS-i certificate	05001	
Mechanical data		
Type of mounting	mounting on DIN rail	
Materials	PA; PVC	
Displays / operating elements		
Display	switching status	LED, yellow
	operation	LED, green
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Connection		



Article no longer available - archive entry

Alternative article: AC2257 When selecting an alternative article and accessories please note that technical data may differ! – When selecting an alternative article and accessories please note that technical data may differ!