




## Jumper cable with valve plug

VVSAB031--S0005A03STGH030MSS

Article no longer available - archive entry



## Electrical data

|                        |     |            |
|------------------------|-----|------------|
| Operating voltage      | [V] | < 24 AC/DC |
| Overvoltage protection |     | yes; (VDR) |

## Operating conditions

|                     |      |          |
|---------------------|------|----------|
| Ambient temperature | [°C] | -25...90 |
| Protection          |      | IP 67    |

## Mechanical data

|                       |                      |
|-----------------------|----------------------|
| Materials             | TPU                  |
| Moulded-body material | TPU                  |
| Material nut          | brass, nickel-plated |

## Displays / operating elements

|         |                  |                 |
|---------|------------------|-----------------|
| Display | switching status | 1 x LED, yellow |
|---------|------------------|-----------------|

## Accessories

|                |                     |
|----------------|---------------------|
| Items supplied | screw               |
|                | panel for labelling |

## Remarks

|               |        |
|---------------|--------|
| Pack quantity | 1 pcs. |
|---------------|--------|




## Jumper cable with valve plug

VVSAB031--S0005A03STGH030MSS

### Electrical connection - plug


Connector: 1 x M12, straight; coding: A; Moulded body: TPU; Locking: brass, nickel-plated



### Electrical connection

Cable: 5 m, PUR / PVC; 3 x 0.5 mm<sup>2</sup>

### Connection



### Electrical connection - socket

Connector: 1 x valve type B industrial standard, angled; Moulded body: TPU; Locking: brass, nickel-plated

