


E80347



RFID tag

ID-TAG/M5x16,5/06



1 middle of the tag



Application

Application	coding of workpiece carriers in routing conveyors	
Operating temperature (active) [°C]	-25...85	
Peak temperature (passive) [°C]	90	

Electrical data

Operating frequency [MHz]	13,56	
Memory size [bit]	896	
Memory type	EEPROM	
Chip type	Vigo	
Number of blocks	28	
Block size [Byte]	4	
Unique Identification Number (UID) [Byte]	8	
RFID standard	ISO 15693	
Max. read cycles	unlimited	
Max. write cycles	100000	

Operating conditions

Ambient temperature [°C]	-25...85	
Storage temperature [°C]	-40...90	
Protection	IP 67	

Tests / approvals

Shock resistance	DIN IEC 68-2-29	30 g 18 ms
Vibration resistance	DIN IEC 68-2-6	6 g 14...200 Hz
Radio approval	ISO 15693	

Mechanical data

Weight [g]	5.3	
Housing	threaded type	
Type of mounting	installation on non-metal materials; (screw fastening ; sticking to a surface)	
Dimensions [mm]	M5 / L = 16.5	
Thread designation	M5	
Materials	PA black	

E80347



RFID tag

ID-TAG/M5x16,5/06

Remarks

Pack quantity	10 pcs.
---------------	---------

Other data

Reading distance when mounted on non-metal (mm)

ANT410 / DTI410	-
ANT411 / DTI411	5
ANT420 / DTI420 / DTM424 / DTI424 / DTM426	-
ANT421 / DTI421 / DTM425 / DTI425 / DTM427	10
ANT430 / DTI430 / DTM434 / DTI434 / DTM436	5
ANT431 / DTI431 / DTM435 / DTI435 / DTM437	15
ANT513 / DTI513 / DTC510	25
ANT515 / DTI515 / ANT516 / DTI516	5
ANT600 / DTI600	15