



Connecting cable with socket

ADOGH040MSN0002H04/1G/1D



Application	
Special feature	Free from silicone; Halogen-free; Gold-plated contacts
Free from silicone	yes
Compatible with paint	yes
Electrical data	
Operating voltage [V]	< 30 DC
Protection class	II
Max. input power [mW]	group II: 1000; group IIIB: 1000; group IIIC: 550 (Ta < 90 °C) / 650 (Ta < 70 °C) / 750 (Ta < 40 °C)
Max. current load total [A]	1
Operating conditions	
Ambient temperature [°C]	-25...90
Note on ambient temperature	for use in hazardous areas: ambient temperature in accordance with unit marking
Protection	IP 67; (when used outside the hazardous area: IP 68 / IP 69K)
Tests / approvals	
Approval	BVS 11 ATEX E 009 X; IECEx BVS 11.0002 X
ATEX marking	II 1G Ex ia IIB T6 Ga Ta: -25...80°C
	II 2G Ex ia IIC T6 Gb Ta: -25...80°C
	II 1D Ex ia IIIC T85°C Da Ta: -25...80°C
	II 1G Ex ia IIB T5 Ga Ta: -25...90°C
	II 2G Ex ia IIC T5 Gb Ta: -25...90°C
	II 1D Ex ia IIIC T95°C Da Ta: -25...90°C

ENC01A




Connecting cable with socket

ADOGH040MSN0002H04/1G/1D

Safety classification		
Max. internal capacitance	[nF]	0.2
Max. internal inductance	[μH]	4
Mechanical data		
Weight	[g]	101.8
Dimensions	[mm]	15.5 x 15.5 x 45
Materials	housing: TPU orange; Sealing: FKM	
Material nut	brass, nickel-plated	
Remarks		
Remarks	Special conditions for safe operation apply for use in hazardous areas.	
	Observe the corresponding notes in the operating instructions (Ex protection related part).	
Pack quantity	1 pcs.	

Electrical connection
Cable: 2 m, PUR, Halogen-free, blue, Ø 4.9 mm; 4 x 0.34 mm ² (42 x Ø 0.1 mm)

Electrical connection - socket
Connector: 1 x M12, straight; coding: A; Locking: brass, nickel-plated; Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm



Connection		
BK =	Core colours :	
BN =	black	
BU =	brown	
WH =	blue	
	white	