


Inductive sensor

IGA4008-CPKG/TS-600-APA

Article no longer available - archive entry

Alternative articles: IG5842

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP
Output function	complementary
Sensing range [mm]	8
Housing	threaded type
Dimensions [mm]	M18 x 1

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	10; (24 V)
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	complementary
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	720
Short-circuit protection	yes

IG5760



Inductive sensor

IGA4008-CPKG/TS-600-APA

Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone	
Sensing range [mm]	8
Real sensing range S_r [mm]	$8 \pm 10\%$
Operating distance [mm]	0...6.5

Accuracy / deviations	
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.4 / copper: 0.3
Hysteresis [% of S_r]	3...15
Switch point drift [% of S_r]	-10...10

Operating conditions	
Ambient temperature [°C]	-25...80
Protection	IP 65

Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data	
Housing	threaded type
Mounting	non-flush mountable
Dimensions [mm]	M18 x 1
Thread designation	M18 x 1
Materials	brass nickel-plated; PBT

Displays / operating elements		
Display	switching status	1 x LED, yellow

Accessories	
Items supplied	lock nuts: 2

Remarks	
Pack quantity	1 pcs.

Electrical connection - plug

Connector: 1 x Ø 28 mm; coding: A



Inductive sensor

IGA4008-CPKG/TS-600-APA

Connection

