



Retro-reflective sensor

OGR-DNKG

Article no longer available - archive entry

Alternative articles: OG5047

When selecting an alternative article and accessories please note that technical data may differ!

No scale drawing available

Product characteristics

Type of light	infrared light
Housing	threaded type

Application

Function principle	Retro-reflective sensor
--------------------	-------------------------

Electrical data

Operating voltage	[V]	10...55 DC
Current consumption	[mA]	10; ((24 V))
Protection class		II
Reverse polarity protection		yes
Type of light		infrared light
Wave length	[Nm]	880

Outputs

Electrical design		NPN
Output function		dark-on mode
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	160
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes



OG5016



Retro-reflective sensor

OGR-DNKG

Detection zone		
Range	[m]	< 3; (Prismatic reflector Ø 80 E20005)
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	class B
	EN 55011	
Mechanical data		
Housing		threaded type
Dimensions	[mm]	M18 x 1
Thread designation		M18 x 1
Materials		brass nickel-plated
Lens material		glass
Displays / operating elements		
Display	switching status	1 x LED, yellow
Accessories		
Items supplied		lock nuts: 2 x
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 2 m, PVC; 3 x 0.5 mm ²		
Connection		



Core colours :

- BN = brown
- BU = blue
- BK = black