

Inductive sensor

II-3010-APKG/PPU

Article no longer available - archive entry

Alternative articles: II5272

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP
Output function	normally closed
Sensing range [mm]	10
Housing	threaded type
Dimensions [mm]	M30 x 1.5 / L = 81

Electrical data

Operating voltage [V]	10...55 DC
Current consumption [mA]	5; (24 V)
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally closed
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	250
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone


Sensing range [mm]	10
Real sensing range S_r [mm]	$10 \pm 10 \%$
Operating distance [mm]	0...8.1



Inductive sensor

II-3010-APKG/PPU

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	
Switch point drift	[% of Sr]	
Operating conditions		
Ambient temperature		[-°C]
Protection		IP 67
Mechanical data		
Housing		threaded type
Mounting		flush mountable
Dimensions		[mm]
Thread designation		M30 x 1.5 / L = 81
Materials		M30 x 1.5
		PBT
Displays / operating elements		
Display		switching status
		1 x LED, yellow
Accessories		
Items supplied		lock nuts: 2
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 2 m, PUR; highly flexible; 3 x 0.5 mm²		
Connection		



Core colours :

BN = brown

BU = blue

BK = black