

PP7542



Pressure switch with ceramic measuring cell


PP-100-SBG14-QFRKG/BS/ /N

Article no longer available - archive entry

Alternative articles: PP7552

When selecting an alternative article and accessories please note that technical data may differ!

Note: electrical connection of the replacement units via M12 socket.



Product characteristics

Output signal	switching signal		
Measuring range	0...100 bar	0...1450 psi	0...10 MPa
Process connection	threaded connection G 1/4 external thread internal thread:M5		

Application

Application	for industrial applications		
Media	liquids and gases		
Conditionally suitable for	For gaseous media the application is limited to max. 25 bar.		
Medium temperature [°C]	-25...90; (on request: -40...90 °C)		
Min. bursting pressure	650 bar	9400 psi	65 MPa
Pressure rating	300 bar	4350 psi	30 Mpa
Type of pressure	relative pressure		

Electrical data

Operating voltage [V]	9.6...30 DC		
Current consumption [mA]	< 45		
Min. insulation resistance [MΩ]	100; (500 V DC)		
Protection class	III		
Reverse polarity protection	yes		
Power-on delay time [s]	0.3		



Pressure switch with ceramic measuring cell

PP-100-SBG14-QFRKG/BS/ /N

Inputs / outputs			
Number of inputs and outputs	Number of digital outputs: 2		
Outputs			
Total number of outputs	2		
Output signal	switching signal		
Electrical design	PNP/NPN		
Number of digital outputs	2		
Output function	normally open / normally closed; (parameterisable)		
Max. voltage drop switching output DC [V]	2		
Permanent current rating of switching output DC [mA]	250		
Switching frequency DC [Hz]	< 170		
Short-circuit protection	yes		
Type of short-circuit protection	pulsed		
Overload protection	yes		
Measuring/setting range			
Measuring range	0...100 bar	0...1450 psi	0...10 MPa
Set point SP	1...99.9 bar	10...1450 psi	0.1...0.99 MPa
Reset point rP	0.5...95.5 bar	10...1440 psi	0.05...9.95 MPa
In steps of	0.1 bar	10 psi	0.01 MPa
Accuracy / deviations			
Switch point accuracy [% of the span]	< ± 1,5		
Repeatability [% of the span]	< ± 0,1; (with temperature fluctuations < 10 K)		
Characteristics deviation [% of the span]	< ± 0,25 (BFSL) / < ± 0,5 (LS); (BFSL = Best Fit Straight Line; LS = limit value setting)		
Linearity deviation [% of the span]	< ± 0,5		
Hysteresis deviation [% of the span]	< ± 0,1		
Long-term stability [% of the span]	< ± 0,1; (per year)		
Temperature coefficient zero point [% of the span / 10 K]	< ± 0,2; (0...80 °C)		
Temperature coefficient span [% of the span / 10 K]	< ± 0,3; (0...80 °C)		
Response times			
Response time [ms]	< 3		
Damping for the switching output dAP [s]	0...4		
Software / programming			
Adjustment of the switch point	programming unit / teach function		

PP7542



Pressure switch with ceramic measuring cell

PP-100-SBG14-QFRKG/BS/ /N

Interfaces

Communication interface	EPS
-------------------------	-----

Operating conditions

Ambient temperature	[°C]	-40...90
Storage temperature	[°C]	-40...100
Protection	IP 68; (BFSL = Best Fit Straight Line; LS = limit value setting)	

Tests / approvals

EMC	radiation of interference	according to the automotive directive 1995/54/EC	
	immunity	according to the automotive directive 1995/54/EC annex IX	
	HF radiated	150 V/m	
	pulse resistance	ISO 7637	
	supply	ISO 7637-2 (Pulse 1a, 1b, 2, 3a, 3b, 4, 6, 7)	
	signal cables	ISO 7637-3 (Pulse a und b)	
	immunity	EN 61000-6-2	
	EN 61000-4-2 ESD	8/15 kV	
	EN 61000-4-3 HF radiated	100 V/m	
	EN 61000-4-4 Burst	2 kV	
	EN 61000-4-6 HF conducted	10 V	
	Shock resistance	DIN IEC 60068-2-27 / DIN IEC 60068-2-29	1000 g
	Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)

Mechanical data

Materials	stainless steel (1.4301 / 304); FKM; PBT
Materials (wetted parts)	stainless steel (1.4305 / 303); ceramics; FKM
Min. pressure cycles	100 million
Process connection	threaded connection G 1/4 external thread internal thread:M5
Restrictor element integrated	no (can be retrofitted)

Displays / operating elements


Display	operation	LED, green
	switching status	2 x LED, yellow
Teach function	yes	

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x Bajonett



PP7542



Pressure switch with ceramic measuring cell

PP-100-SBG14-QFRKG/BS/ IN

