


## Capacitive sensor

KB-3020-APKG/NI/10M/PH

Article no longer available - archive entry



## Product characteristics

Electrical design	PNP
Output function	normally closed
Sensing range [mm]	3...20
Housing	cylindrical
Dimensions [mm]	Ø 34 / L = 81

## Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	13; (24 V)
Protection class	II
Reverse polarity protection	yes

## Outputs

Electrical design	PNP
Output function	normally closed
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	40
Short-circuit proof	yes
Overload protection	yes

## Detection zone

Sensing range [mm]	3...20
Sensing range adjustable	yes
Factory setting sensing range [mm]	20
Real sensing range $S_r$ [mm]	$20 \pm 10 \%$
Operating distance [mm]	0...16.2

## Accuracy / deviations

Correction factor	glass: 0.4 / water: 1 / ceramics: 0.2 / PVC: 0.2
Hysteresis [% of $S_r$ ]	1...15



## Capacitive sensor

KB-3020-APKG/NI/10M/PH

Switch point drift	[% of Sr]	-15...15
--------------------	-----------	----------

## Operating conditions

Ambient temperature	[°C]	-25...70
Protection		IP 65
Increased immunity		yes; (increased immunity to conducted radio frequency interference)

## Tests / approvals

EMC	EN 60947-5-2
-----	--------------

## Mechanical data

Housing		cylindrical
Mounting		non-flush mountable
Dimensions	[mm]	Ø 34 / L = 81
Materials		PBT

## Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

## Accessories

Items supplied	Mounting clamps: 1
	screwdriver: 1


## Remarks

Pack quantity	1 pcs.
---------------	--------

## Electrical connection

Cable: 10 m, PUR; 3 x 0.5 mm<sup>2</sup>

## Connection



	Core colours :
BN =	brown
BU =	blue
BK =	black